



EMPTY ENCLOSURE

# TG PC 3023-11-0


## TG PC 3023-11-0

Empty enclosure

**CUSTOMIZE**

302 x 232 x 110 mm  
Article number: 20091301

Empty enclosure - Industrial Quality -, Base and cover: Polycarbonate, light grey similar to RAL 7035, with quick closing, with cover retainer



## Technical data

### Measures

Width:	302 mm
Length:	232 mm
Height:	110 mm
Inner height:	94 mm

### Material:

Box:	polycarbonate, grey similar RAL 7035
Cover:	polycarbonate, grey similar RAL 7035
Sealing:	Polyurethane
Cover screw:	stainless steel V2A, fast-closing
material:	Polycarbonate

## Accessory

- DAE M12 - Pressure balance element
- LFR - Stepped drill
- NS 35-283,5 - Standard rail
- TG ABL - External fixing lugs kit
- TG DVS-57 - Cover retainer
- TG ISS - Interior hinge set
- TG MPI-3023 - Mounting plate
- TG MPS-3023 - Mounting plate
- TG PST2 - Sealing kit
- TS 15-283,5 - Standard rail



EMPTY ENCLOSURE

# TG PC 3023-11-o

## Other attributes

Ingress protection:	IP66/IP67 acc. EN 60529 / DIN VDE 0470-1
Impact resistance:	IK08 acc. DIN EN 5012 / VDE 0470 segment 100
Protection class:	II - isolate protection acc. VDE 0106
Rated insulation voltage AC:	690 V
Rated insulation voltage DC:	1000 V
Heavy metals-free:	Yes
PVC-free:	Yes
Silicone-free:	Yes
Cable entries:	No
Combustion behaviour to UL 50 / UL 746C:	5VA nach UL 50 / UL 746C
Combustion behaviour acc. to UL 94:	V-2 acc. UL 94
Combustion behaviour acc. to VDE:	960°C acc. VDE 0471/ EN 60695
weatherproof:	Yes - acc. to UL 746 C

## Environmental attributes

Ambient temperature (min.):	-35 °C
Ambient temperature (max.):	80 °C
Ambient temperature (24 h):	60 °C
Max. rel. humidity at 25° C (short term):	95%
Max. rel. humidity at 40° C:	50%