



**3** JAHRE  
 YEARS  
 GARANTIE  
 WARRANTY

## ANSMANN HD500R

- High-quality, multifunctional head lamp made from aluminium and robust ABS plastic
- Simple focussing on the lamp head
- Including high-quality ANSMANN 18650 li-ion rechargeable battery with 2600mAh
- LED technology with a super-bright 10W Cree-XM-L2 LED
- Head light can be individually adjusted with an incline angle up to ca. 90°
- The flexible and adjustable head band ensures that it is comfortable to wear (just 161g incl. rechargeable battery)
- IP64 protection rating (protected from dust and splashed water)
- Four light functions: 100% | 50% | 25% | Strobe
- Brightness / Battery life: 550lm - 3h 15min | 275lm - 7h | 110lm - 19h
- Light range: max. 160m
- 3 year ANSMANN guarantee

## INFORMATION

Product name	HD500R
Part No.	1600-0325
EAN-Code	4013674125425
Customs tariff number	8513100000
Product content	HD500R, USB charge cable, operating instructions

Product	37 × 85 × 50 mm / 131 g
Packing + Product	125 × 73 × 272 mm / 263 g
Packing Unit	6 (444 × 131 × 284 mm)

