


**SPECIFICATIONS**  
 Current Rating: 3A AC,DC  
 Voltage Rating: 250V AC,DC  
 Temperature Range: -25°C ~ +85°C  
 Contact Resistance: 30mΩ Max.  
 Insulation Resistance: 1000MΩ Min.  
 Withstanding Voltage: 650V AC/minute  
 Pin Material: Brass/Gold-flash  
 Material: Nylon 6T,UL94V-0  
 Color: Natural(Black)



**Ordering Information & Dimensions**

PART NO.	Dimensions	
	A	B
A2005WV-02P	2.00	6.00
A2005WV-03P	4.00	8.00
A2005WV-04P	6.00	10.00
A2005WV-05P	8.00	12.00
A2005WV-06P	10.00	14.00
A2005WV-07P	12.00	16.00
A2005WV-08P	14.00	18.00
A2005WV-09P	16.00	20.00
A2005WV-10P	18.00	22.00
A2005WV-11P	20.00	24.00
A2005WV-12P	22.00	26.00
A2005WV-13P	24.00	28.00
A2005WV-14P	26.00	30.00
A2005WV-15P	28.00	32.00

UNIT	SCALE	SHEET	TITLE:
mm		1 of 1	
DRAWN BY	APPROVED BY	2.00mm PITCH 180° WAFER	
董正一 2005.04.16	董正一 2005.04.16		
GENERAL TOLERANCE			
B1	REVISE	2006.12.12	X. X±0.25
B0	NEW RELEASE	2005.11.24	X. XX±0.15
REV.	DESCRIPTION	DATE	X. XXX±0.05
DRAW NO.:			REV.:
A2005WV-XP			B1