
THESE DRAWINGS ARE THE PROPERTY OF QUALTEK ELECTRONICS AND NOT TO BE REPRODUCED FOR OR COMMUNICATED TO A THIRD PARTY WITHOUT THE EXPRESS WRITTEN PERMISSION OF AN OFFICER OF QUALTEK ELECTRONICS.

REVISION							
REV.	DESCRIPTION	DATE	APPROVED				



NOTES:

1. CABLE: UL2725

28AWGx1PR+24AWGx2C+ AEB(AL) 65% OUTER JACKET: BLACK, OD: 4.5 ± 0.2mm

2. CONNECTOR: USB 2.0 A TYPE MALE

INSULATOR: WHITE PBT

PIN G/F

NICKEL PLATED SHELL

3. CONNECTOR: MICRO USB 2.0 (B) 5P/M TYPE MALE

INSULATOR: BLACK PBT

PIN G/F

NICKEL PLATED SHELL

- 4. PVC MOLDED: COLOR 45P BLACK
- 5. ELECTRICAL TEST:
 - <1>.100% OPEN SHORT & MISS WIRE TEST
 - <2>.INSULATION RESISTANCE: AC 300V DC300V 10M ohm MIN.
 - <3>. CONDUCTOR RESISTANCE: 1 ohm MAX.
- 6. PACKING: 1PC/POLYBAG W/ LABEL

CONNECTION

CN1	CN2
1 RED	1
2	2 2 3
4BLAC	CK 5
SHELL—BRAID&I	DRAIN- SHELL

CONTROLLED

Dim range (mm)	Tolerance +/- (mm)	Qualtek Electronics Corp. WCI DIVISION Part Number: 3021077-10 Rohs Compliant		
0-1	0.15	Description: USB 4P(A)/M - MICRO USB 5P(B)/M		
1-6	0.20			
6-18	0.30		LINUT	
18-50	0.50		UNIT: mm	
50-120	0.70	Drawn / Date	Checked / Date	Approved / Date
120-250	0.90	R. Nuti	04-06-18	LY / 04-06-18
250-500	1.20	04-06-18	04-00-10	217 04 00-10

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Qualtek: 3021077-10