

D-Sub Subminiature D connectors**D-Sub, MA AWG 24-28 crimp cont**

Crimp contact, Turned, Male, Copper alloy, Conductor cross-section: [0,09] ... [0,25 mm²], AWG 24 ... AWG 28

Part number: **09 67 000 7576**



Please [login](#) or [register](#) for a free MyHARTING Account to see all information about product availability and your order.

Technical data**Identification**

Category	Contacts
Series	D-Sub
Identification	Standard
Type of contact	Crimp contact
Description of the contact	Turned

Version

Gender	Male
Performance level	1
Pack contents	Single contact

Technical characteristics

Conductor cross-section	0.09 ... 0.25 mm²
Conductor cross-section	AWG 24 ... AWG 28
Contact resistance	≤ 10 mΩ
Stripping length	4 mm

Material properties

Material (contacts)	Copper alloy
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes

REACH SVHC substances**Lead****Commercial data****Packaging size****100****Net weight****0.2 g****Country of origin****Switzerland****European customs tariff number****85366990****Combinables****Modules****Han Gigabit insert male**

09 14 008 3011

Tools**Tools**

Locator D-Sub turned standard contacts

09 99 000 0531