



629-2RS

SKF Explorer

Dimensions

d	9	mm
D	26	mm
B	8	mm
d ₂	≈ 12.55	mm
D ₂	≈ 22.6	mm
r _{1,2}	min. 0.3	mm

Abutment dimensions

d _a	min.	11.4	mm
d _a	max.	12.5	mm
D _a	max.	23.6	mm
r _a	max.	0.3	mm

Calculation data

Basic dynamic load rating C	4.8	kN
Basic static load rating C ₀	2	kN
Fatigue load limit P _u	0.083	kN
Limiting speed	19000	r/min
Calculation factor k _r	0.025	
Calculation factor f ₀	12	

Mass

Mass bearing	0.02	kg
--------------	------	----