DIN Plug Connector

Features

- RoHS and REACh compliant
- Fits most communication radios
- Solder terminal
- Microphone connector with thread locking

Specification



Panel Hole Diameter	16 mm	
Gender	Plug	
Mounting Type	Panel Mount	
Number of Poles	2	
Mating Type	Thread-Lock	
Orientation	Straight	
Operating Temperature	0 60 °C	
Voltage Rating	125 V	
Wire Cross-Section max.	1.5 mm²	
Insulation Resistance	1.5 GOhm	
Contact Resistance	10 MOhm	
Current Rating	7 A	

Material Specification

Housing Material	Nickel Plated Copper
Contact Material	Nickel-Plated Copper

Drawing



