



**1-CONDUCTOR PCB TERMINAL
STRIP 1 SOLDER PIN/POLE IN LINE
PIN SPACING 7.5 MM / 0.295 IN WITH
PUSH BUTTONS
250-602 TO 250-612**

ITEM-NO. (ITEM-NO.)	250-603
Cross section1 (Cross section / mm²)	0.5 - 1.5
Cross section2 (Cross section / AWG)	20 - 14
Strip length (Strip length / mm)	9 - 10
Measured voltage (Measured voltage / V)	630
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	17.5
RM (PIN SPACING / mm)	7.5
P (NO. OF POLES)	3
Height (Height / mm)	16.5
Width (Width / mm)	21.5
Depth (Depth / mm)	13
No. of connection Points (No. of connection Points)	3
No. of potentials (No. of potentials)	3
COLOR (COLOR)	grau
WEIGHT (WEIGHT / g)	3.67
Comment (Comment)	L1 = (No. of poles x Pin Spacing) + 5 mm + 1, 5 mm
Dimensions (Dimensions)	1,2 -0,1 mm