

**W-Series  
WQV 16/4**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Product image**

Similar to illustration

**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

Type	WQV 16/4
Order No.	<a href="#">1055260000</a>
Version	W-Series, Cross-connector, For the terminals, Number of poles: 4
GTIN (EAN)	4008 190037000
Qty.	50 pc(s).

Creation date 11 March 2020 11:19:04 CET

Catalogue status 06.03.2020 / We reserve the right to make technical changes.

**Data sheet**

**W-Series  
WQV 16/4**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Width	10.4 mm	Width (inches)	0.409 inch
Height	45.2 mm	Height (inches)	1.78 inch
Depth	27 mm	Depth (inches)	1.063 inch
Net weight	15.08 g		

**Temperatures**

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	130 °C		

**Material data**

Material	PA 66	Colour	yellow
UL 94 flammability rating	V-0		

**System specifications**

Version	For the terminals
---------	-------------------

**Additional technical data**

Installation advice	Direct mounting	Type of fixing	when screwed in
---------------------	-----------------	----------------	-----------------

**Cross-connector**

Number of cross-connected terminals	4	Rated current, 2-pole	101 A
Rated current, multi-pole	101 A	Tightening torque range for fixing screw	1.2...2.4 Nm
Type	Cross-connector		

**Dimensions**

Pitch in mm (P)	11.9 mm
-----------------	---------

**Rating data**

Rated current	101 A
---------------	-------

**Classifications**

ETIM 6.0	EC000489	ETIM 7.0	EC000489
eClass 9.0	27-14-11-40	eClass 9.1	27-14-11-40
eClass 10.0	27-14-11-40	UNSPSC	30-21-18-01

**Approvals**

Approvals	
ROHS	Conform

**Data sheet****W-Series  
WQV 16/4**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technical data****Downloads**

---

Brochure/Catalogue	<a href="#">CAT 1 TERM 16/17 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>
Engineering Data	<a href="#">08874_WQV_16-4_DXF.dxf</a> <a href="#">STEP</a>
User Documentation	<a href="#">Beipackzettel_WQV.pdf</a> <a href="#">StorageConditionsTerminalBlocks</a>

---