

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5037640201](#)
Status: **Active**
Overview: [Pico-Lock Connector System](#)
Description: 1.00mm Pitch Pico-Lock Crimp Housing, 1.50mm Mated Height, Positive Side Locks, 2 Circuits

Documents:

3D Model	Application Specification AS-503764-002-001 (PDF)
Drawing (PDF)	Packaging Specification SPK-503764-001-001 (PDF)
Product Specification PS-503764-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-503764-001-001 (PDF)	Product Literature (PDF)



Series image - Reference only

Agency Certification

UL E29179

General

Product Family	Crimp Housings
Series	503764
Application	Signal, Wire-to-Board
Overview	Pico-Lock Connector System
Product Literature Order No	987650-9061
Product Name	Pico-Lock
UPC	887191579344

Physical

Circuits (maximum)	2
Color - Resin	Black
Flammability	SC-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	N/A
Lock to Mating Part	Yes
Material - Resin	High Temperature Thermoplastic
Net Weight	16.000/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Electrical

Current - Maximum per Contact 1.5A

Material Info

Reference - Drawing Numbers

Application Specification	AS-503764-001-001, AS-503764-002-001
Packaging Specification	SPK-503764-001-001
Product Specification	PS-503764-001-001
Sales Drawing	SD-503764-001-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[503764](#) Series

Mates With

[503763](#) Pico-Lock Wire-to-Board Header

Use With

[503765](#) Pico-Lock Crimp Terminal