

TECHNIC line ELECTRONIC PLIERS



from high quality ball bearing steel (Chrome-steel) for extreme high efforts.
 The inductive hardened cutting edges achieve a value of 63 - 65 HRC.
 Precision joint with screw system - precise jaw adjustment without backlash,
 non-reflective surface. Double leaf spring in stainless steel.
 Ergonomically formed bicoloured hand guard from dissipative anti-slide material.

No.	Length mm	Head- width mm	Finish	Cutting capacity			Weight g
				Wire soft	mm medium	Ø hard	

Side cutters

with slim, rounded head

3-961-15	120	10	Semi Flush	1.3	0.8	0.5	75
3-963-15	120	10	Ultra Flush	1.3	0.7	-	75

Side cutters

with slim, pointed head

3-964-15	120	10	Semi Flush	1.2	1.0	0.5	75
3-966-15	120	10	Ultra Flush	1.0	0.8	-	75

Side cutters

with slim, pointed and relieved head

3-967-15	120	10	Semi Flush	0.8	0.6	-	75
3-969-15	120	10	Ultra Flush	0.8	-	-	75

Side cutters

with rounded head

3-971-15	125	12,5	Semi Flush	1.6	1.0	0.5	80
3-973-15	125	12,5	Ultra Flush	1.6	0.8	-	80

End cutters

with slim, pointed head, special flat cutting edge
 and adjustable stop screw

3-981-15	135	10	Ultra Flush	0.8	0.6	-	80
----------	-----	----	-------------	-----	-----	---	----

Wire lead catcher

3-999-1	3-961-15 until 3-969-15 (10 mm Head-width)						9
3-999-2	3-971-15 until 3-973-15 (12.5 mm Head-width)						9

Round nose pliers

extremely slim

3-991-15	130	10	short plain jaws				75
----------	-----	----	------------------	--	--	--	----

Flat nose pliers

extremely slim

3-992-15	130	10	short plain jaws				75
----------	-----	----	------------------	--	--	--	----


Snipe nose pliers

extremely slim


3-996-15	140	10	long plain jaws				80
----------	-----	----	-----------------	--	--	--	----




3-961-15



3-967-15




3-964-15



3-981-15



3-971-15



3-992-15



3-991-15



3-999



3-996-15