

FEATURES

- Single handed operation
- Light and compact
- Safety version
- Silicon free

RS PRO MALE PLUG ISO 6150 A6 – 2.5 mm

RS Stock No.: 2312500



RS PROfessionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO male plug – 2.5 mm works in 0 to 10 bar pressure range. It mainly used in compressed air & tools, pneumatic & fluid technology, food & beverages. It is available in nickel-plated brass. Used for compressed air and for moulding injection cooling system. RoHS and REACH compliant. Operating temperature range is from - 20 °C to + 80 °C.

General Specifications


Material	Brass
Applications	Lubrication System, Cooling System, Pneumatic Machinery Equipment

Mechanical Specifications

Connection Type	Threaded
Coupling Gender	Male
Threaded Connection	1/8 in Male BSP
Thread Size	1/8in
Wrench Size	6 Hex
Length	26.5mm

Similar Products

Parameters	2312521	2312522
Brand	RS PRO	RS PRO
Connection Type	Threaded, Tube	Threaded, Tube
Tube Connection Size	9	10
Coupling Gender	Male	Male
Threaded Connection	3/8 in Male	1/2 in Male
Thread Size	3/8in	1/2in
Hose Barb Connection	30.5mm	25Hex
Wrench Size	20Hex	54mm



A	B	C	CH	Pack.
1/8	6	26.5	11	10