



| | 16 Amp | | 32 Amp | |
|--|---------------|------|---------|---------|
| Pole | 4 | 5 | 4 | 5 |
| a | 128 | 134 | 150 | 155 |
| b | 92 | 98 | 104 | 109 |
| c | 53 | 61 | 63 | 70 |
| K_Kabel Ø [mm] | 6-15 | 8-16 | 11,5-20 | 11,5-22 |
| Anschlussart: | Schraubklemme | | | |
| Leitung flexibel Klasse 5 oder 6 [mm ²] | 1-2,5 | | 2,5-6 | |
| Kontaktschrauben [Ncm] | 100 Ncm | | 110 Ncm | |
| SW | 42 | 42 | 50 | 50 |
| Gewicht [g] | 131 | 154 | 204 | 236 |