



	16 Amp			32 Amp		
Pole	3	4	5	3	4	5
a	133	138	145	161	161	168
b	76	80	89	91	94	100
K_Kabel Ø [mm]	6-15	6-15	8-16	11,5-20	11,5-20	11,5-22
Anschlussart:	Schraubklemme					
Leitung flexibel [mm ²]	1-2,5			2,5-6		
Kontaktschrauben [Ncm]	100 Ncm			110 Ncm		
SW	42	42	42	50	50	50
Gewicht [g]	142	161	189	229	244	294