

## Han M23 Hood 7-12 mm



Part number	09 15 100 0402
Specification	Han M23 Hood 7-12 mm
HARTING eCatalogue	<a href="https://b2b.harting.com/09151000402">https://b2b.harting.com/09151000402</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> M23 Signal
Type of hood/housing	Hoods
Description of hood/housing	EMC version

### Version

Locking type	Screw locking
Size	M23
Version	Top entry

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP67 in locked position IP69 / IPX9K acc. to ISO 20653 in locked position
Clamping range	7 ... 12 mm

### Material properties

Material (hood/housing)	Copper-zinc alloy
Surface (hood/housing)	Nickel plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No



Pushing Performance

## Material properties

REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
----------	-----------------------

## Commercial data

Packaging size	1
Net weight	77.1 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors