


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	ECR-20-004655	06OCT20	RK	SBH

NOTE:

- PACKAGING ACC. TO TE SPEC.107-18032
BUNDLE EVERY 25 ASSEMBLIES WITH A RUBBER BAND
- ELECTRICAL TEST CONTAINING "SHORT CIRCUIT TEST, CONTINUITY AND ACCURATE CAVITY ASSIGNMENT TEST" ACC. TO TE-SPEC.108-18857, SUBSECTION 3.1.1
- WIRING SCHEDULE AS SHOWN
- ASSEMBLY IN COLORS BLACK AND WHITE
- CABLES TO USE IN MEXICO FACTORY ONLY.



5	FT	L	-	CABLE AWC 8126 WHITE, 4/22AWG, UL 2464	9
	FT	-	L	CABLE AWC 8126 BLACK, 4X22AWG, UL 2464	8
	FT	L	-	CABLE LIYY 4xAWG22 UL 2464 WH	7
	FT	-	L	CABLE LIYY 4xAWG22 UL 2464 BK	
	PC	4	4	MICRO QUADLOK SYSTEM PIN CONTACT	6
	PC	4	4	MICRO QUADLOK SYSTEM SOCKET CONTACT	5
	PC	1	1	4 POS. LOW VOLTAGE CONN.M.POSITIONER	4
	PC	1	1	4 POS. LOW VOLTAGE CONN.F.POSITIONER	3
	PC	-	1	4 POS. LOW VOLTAGE MALE CONN.HSG BK	2
	PC	1	-	4 POS. LOW VOLTAGE MALE CONN.HSG WH	
	PC	-	1	4 POS. LOW VOLTAGE REC.CONN.HSG BK	1
	PC	1	-	4 POS. LOW VOLTAGE REC.CONN.HSG WH	
	UOM	QTY	QTY	DESCRIPTION	POS.
		2--X	1--X		

WIRING SCHEDULE 3

SIDE A	COLOR	SIDE B
M1	BN	F1
M2	RD	F2
M3	OG	F3
M4	BK	F4

	PN	L/ft	TOLERANCES/ft
	X-2083136-1	2	+/-0.01
OBSOLETE	X-2083136-2	4	+/-0.02
OBSOLETE	X-2083136-3	8	+/-0.03
OBSOLETE	X-2083136-4	12	+/-0.05

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -
FINISH	-

MATERIAL: -

DWN: 25FEB11 SATHISH KUMAR.G

CHK: 02MAR11 R.HOSSAINI

APVD: 02MAR11 R.HOSSAINI

NAME: CABLE ASSEMBLY NECTOR S LINE UL 4 POS., MALE TO FEMALE

PRODUCT SPEC: -

APPLICATION SPEC: -

WEIGHT: -

SIZE: A3 CAGE CODE: 00779 DRAWING NO: C-2083136 RESTRICTED TO: -

CUSTOMER DRAWING SCALE: NTS SHEET: 1 OF 1 REV: B1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-2083136-1](#)