

## FEATURES

- All fluids usable in aggressive environment
- Mechanical resistance
- Silicon free

# RS PRO NON RETURN VALVE 316L FEM-FEM 1/8

RS Stock No.: 2312703



RS PROfessionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

The RS PRO non return valve 316L fem-fem 1/4 works in 0.2 bar to 25 bar pressure range. It is mainly used in chemical, petrochemical, life & sciences, inert gases and vacuum applications. It is also usable in salty environment and on machines that need frequent washing with aggressive detergents. RoHS and REACH compliant.

## General Specifications

<b>Minimum Operating Pressure</b>	0.2bar
<b>Maximum Operating Pressure</b>	25bar
<b>Application</b>	Robotics, Automotive, Textile, packaging and handling, Vacuum, Industrial water, Compressed air circuit

## Mechanical Specifications


<b>Inlet Connection Type</b>	Threaded
<b>Threaded Inlet Connection</b>	1/4 in Female
<b>Outlet Connection Type</b>	Threaded
<b>Threaded Outlet Connection</b>	1/4 in Female
<b>Wrench Size</b>	13mm
<b>Length</b>	44mm

## Operation Environment Specifications

<b>Operating Pressure Range</b>	0.2bar to 25bar
---------------------------------	-----------------

## Similar Products

Parameters	2312704	2312702
Brand	RS PRO	RS PRO
Minimum Operating Pressure	0.2bar	0.2bar
Maximum Operating Pressure	25bar	25bar
Inlet Connection Type	Threaded	Threaded
Threaded Inlet Connection	3/8 in Female	1/4 in Female
Outlet Connection Type	Threaded	Threaded
Threaded Outlet Connection	3/8 in Female	1/4 in Female
Wrench Size	24mm	13mm
Length	50mm	44mm



A	B	L	CH	Pack.
1/4	11	44	17.00	2