

FEATURES

- All fluids usable in aggressive environment
- Mechanical resistance
- Silicon free

RS PRO NON RETURN VALVE 316L FEM-FEM 3/8

RS Stock No.: 2312704



RS PROfessionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO non return valve 316L fem-fem 3/8 works in 0.2 bar to 25 bar pressure range. It is mainly used in chemical, petrochemical, life & sciences, inert gases and vacuum applications. It is also usable in salty environment and on machines that need frequent washing with aggressive detergents. RoHS and REACH compliant.

General Specifications

Minimum Operating Pressure	0.2bar
Maximum Operating Pressure	25bar
Application	Robotics, Automotive, Textile, packaging and handling, Vacuum, Industrial water, Compressed air circuit

Mechanical Specifications


Inlet Connection Type	Threaded
Threaded Inlet Connection	3/8 in Female
Outlet Connection Type	Threaded
Threaded Outlet Connection	3/8 in Female
Wrench Size	24mm
Length	50mm

Operation Environment Specifications

Operating Pressure Range	0.2bar to 25bar
---------------------------------	-----------------

Similar Products

Parameters	2312703	2312702
Brand	RS PRO	RS PRO
Minimum Operating Pressure	0.2bar	0.2bar
Maximum Operating Pressure	25bar	25bar
Inlet Connection Type	Threaded	Threaded
Threaded Inlet Connection	1/8 in Female	1/4 in Female
Outlet Connection Type	Threaded	Threaded
Threaded Outlet Connection	1/8 in Female	1/4 in Female
Wrench Size	16mm	13mm
Length	38mm	44mm



A	B	L	CH	Pack.
3/8	12	58	24.00	2