




## -1. Pliers

### -1.1. SIDE CUTTERS

- Heavy duty side cutting pliers developed according to the scientific ERGO™ process
- ISO 5749
- Finish: Black finish, anti-corrosion treated
- Material: High performance alloy steel, ERGO™ handles with 2-component combination, thermoplastic surface on tough polypropylene which gives superior grip
- Induction hardened cutting edges
- Heavy-duty cutting edge
- Screw joint that provides excellent running and accurate alignment of the cutting edges
- The distance from the joint to the centre of the cutting edges is reduced: Giving greater leverage and increased cutting capacity
- Metal frame designed to enhance accessibility in confined spaces
- Equipped with a patented return spring featuring an on/off function
- IP: Industrial packed

### Side cutting pliers

21HDG



				A mm	B mm	C mm	D mm	E mm			
<b>21HDG-140</b>		7314150231331	5	140	15.9	21.0	8.0	2.0	2.2	2.2	110
<b>21HDG-160</b>		7314150231355	5	160	18.0	23.0	9.0	2.1	2.5	2.5	150
<b>21HDG-180</b>		7314150231379	5	180	19.8	25.0	10.0	2.3	2.8	2.8	210
<b>21HDG-200</b>		7314150231409	5	200	22.4	27.0	10.0	2.8	3.2	3.0	270
<b>21HDG-140IP</b>		7314150231348	5	140	15.9	21.0	8.0	2.0	2.2	2.2	110
<b>21HDG-160IP</b>		7314150231362	5	160	18.0	23.0	9.0	2.1	2.5	2.5	150
<b>21HDG-180IP</b>		7314150231386	5	180	19.8	25.0	10.0	2.3	2.8	2.8	210
<b>21HDG-200IP</b>		7314150231416	5	200	22.4	27.0	10.0	2.8	3.2	3.0	270