


THIS DRAWING IS UNPUBLISHED.      RELEASED FOR PUBLICATION  
 © COPYRIGHT - By -      ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
H	-	A	INITIAL RELEASE	04DEC2013	GSK	BvH
		A1	ECR-14-014684	02OCT2014	GSK	BvH

NOTES:  
 Tolerances cable lengths:  
 0m to 0.5m    +30mm  
 0.5m to 1.0m    +50mm  
 1.0m to 3.0m    +100mm  
 < 3.0m          +1.5%



TECHNICAL DATA	
Operating voltage	max. 30 V AC/DC
Operating current per contact	max. 2 A
Locking of ports	Screw thread M12 x 1 mm (recommended torque 0.6 Nm) self-securing
Protection	IP65 and IP67 when plugged and screwed down (EN 60529)

PUR CABLE	
No./diameter of wires	8 x 0.25 mm <sup>2</sup>
Wire isolation	PP (br, wh, bl, bk, gr, pk, vi, or)
C-track properties	2 million
Jacket	PUR (UL/CSA)
Outer diameter	approx. 6.0 mm
Bend radius (moving)	10 x outer diameter
Temperature range (fixed)	-40...+80 °C
Temperature range (mobile)	-20...+80 °C



8 pos	2.0mtr	PUR	Grey	2273115-5	8x24AWG PUR 2.0m	5
	1.5mtr			2273115-4	8x24AWG PUR 1.5m	4
	1.0mtr			2273115-3	8x24AWG PUR 1.0m	3
	0.6mtr			2273115-2	8x24AWG PUR 0.6m	2
	0.3mtr			2273115-1	8x24AWG PUR 0.3m	1
	LENGTH "L"	MATERIAL	JACKET COLOR	TE PN	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 04DEC2013 SATHISH KUMAR .G	<b>STE</b> TE Connectivity			
DIMENSIONS: mm		CHK 04DEC2013 B.VELDHOVEN				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 04DEC2013 A.VAN ZANDVOORT	NAME M12 STRGT PLUG TO M12 STRGT SOCKET AA			
0 PLC ± -		PRODUCT SPEC	108-19483			
1 PLC ± -		APPLICATION SPEC	114-32127			
2 PLC ± -		WEIGHT	-			
3 PLC ± -		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
4 PLC ± -		A3		00779	C-2273115	-
ANGLES ± -		CUSTOMER DRAWING				SCALE
FINISH		-				NTS
		SHEET				1 OF 1
						REV
						A1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2273115-4](#)