

Search Results

- Evaluate
  - FAQ's
- Design a Solution
  - Part Drawings
  - PDFMilitary Sta ..
- How to Buy
  - Bill of Material
  - Favorite Products List
  - Locate Distributor


Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips

 Text Search: 'GE128-C'

Your search criteria matched only one product, shown below

**GE128-C**



Part Number	GE128-C
RoHS Compliancy Status	Compliant
Part Description	Military Specification Nylon Grommet Edging in 12.75" strips.
Material	Nylon 6.6
Color	Natural
Military Specification	MS21266-3N
Height (In.)	.16
Height (mm)	3.9
Length (In.)	12.75
Length (mm)	323.9
Width (In.)	.22
Width (mm)	5.6
CE Compliant	No
CE Marking	No
Flammability Rating	UL94 V-2
Outside Depth (In.)	.155
Outside Depth (mm)	3.9
Outside Width (In.)	.220
Outside Width (mm)	5.6
Panel Thickness Range (In.)	.085 – .128
Panel Thickness Range (mm)	2.2 – 3.3
Pricing Description	Grommet Edging, Slot Strip, Nylon, Natural
Temperature Range	-40°F to 149°F (-40°C to 65°C)
Min. Order UOM	PC
Min. Order Qty.	100
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.