

MILAN S.r.l. a socio unico

Head Office – Export department:
 Viale Europa, 74
 20090 Cusago (MI) Italy
 T. +39 02 9039.4556-4158
 F. +39 02 9039.4551
 www.taskercables.com

Ufficio Commerciale e Centro Distribuzione
 Viale Europa 72 Strada F12
 20090 Cusago (MI) Italy
 T. +39 02 9039.0037-0059
 F. +39 02 9039.0049
 www.tasker.it

Technical Datasheet ✓RoHS₃

tasker® C105 TN – 2x0,75 mm²

Transparent Divisible Flat Cable



A

B

CATEGORY Flexible Audio Cable (See Audio Catalogue)
APPLICATIONS Speaker and Home Theatre installation

- A:** Transparent **PVC** Sheath.
 Outer Dim. Ø 2,40x4,80 (±0,20) mm.
- B:** One conductor of O.F.C. tinned copper and one of O.F.C. Red Copper.
 Stranded Formation with 0,20 mm.
 Nominal cross section 2x0,75 mm²

MARKING tasker® C105 TN 2x0.75 mm² – O.F.C. SPEAKER CABLE MADE IN ITALY
CUSTOM This product may be custom produced also in **L.S.Z.H.** polymer, **PE,PUR**,
PRODUCTION

Conductors Properties

Conductor Resistance	21,93 Ω/Km
Max Rated Voltage	49 V
Operative Temperature	-15/+70°C

USE	X	Indoor	Interno Edificio	INSTALLATION	X	Fixed	Fissa	INFORMATION	X	RoHS3 Compliant
Impiego		Outdoor Limited	Esterno Limitato	Posa	X	Restricted Mobile	Mobile Limitata	Informazioni	X	Ver. B / 16.05.19
		Outdoor	Esterno			Mobile	Mobile			
		Outdoor Direct Burial	Esterno Interrato			Mobile in Drag Chain	Mobile in Catena			