

<b>Specifications</b>	<b>Range</b>	<b>Best Accuracy</b>
<b>Model</b>		<b>UT802</b>
DC Voltage (V)	200mV/2V/20V/200V/1000V	±(0.1%+3)
AC Voltage (V)	2V/20V/200V/750V	±(0.5%+20)
DC Current (A)	200μA/2mA/20mA/200mA/10A	±(0.5%+20)
AC Current (A)	2mA/20mA/200mA/10A	±(0.8%+40)
Resistance (Ω)	200Ω/2KΩ/20KΩ/200KΩ /2MΩ/200MΩ	±(0.5%+10)
Capacitance (F)	20nF/2μF/200μF	±(4%+10)
Frequency (Hz)	2kHz/200kHz	±(1.2%+10)
Temperature (°C)	-40 °C ~ 1000°C	±(1.2%+25)
<b>Features</b>		
Max Display		19999
Manual Range		√
Diode		√
Transistor		√
Continuity Buzzer		√
Low Battery Indication		√
Data Hold		√
LCD Backlight		√
Input Impedance	≥10MΩ	√
Misuse Alarm		√
<b>General Characteristics</b>		
Power	AC 220V/50Hz or 1.5V batteries (2#) × 6	
LCD Size	108mm × 34.5mm	
Product Color	Red and grey	
Product Net Weight	1650g	
Product Size	300mm × 245mm × 105mm	
Standard Accessories	Test Lead, Alligator Clip, Point Contact Temperature Probe, Multi-Purpose Socket, Power Adapter	
Standard Individual Packing	Gift Box, User Manual	
Standard Quantity Per Carton	4pcs	
Standard Carton Measurement	680mm×365mm×320mm	
Standard Carton Gross Weight	11.7kg	