




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	T4	REVISED PER ECN-22-150900	22APR2022	RK	CSD



- 1 STAMP AMP 8* APPROX AS SHOWN
- 2 UL LISTED E13288, 8 AWG STRANDED
- 3 CSA CERTIFIED LR7189, 8 AWG SOLID OR STRANDED
- 4 NOTE DELETED
- 5 SUPERSEDED BY 8-33461-1
- 6 TIN PLATE 0.00254 [.000100] MIN THK PER ASTM B545
- 7 NOTE DELETED
- 9 NOTE DELETED
- 10 UL 486 A-B



2 3	6	100	LOOSE PIECE, BOX	8-33461-1
2 3	6	1000	33461 TAPE MOUNTED ON 30.48[1.200] CENTERS	2-33461-3
2 3	6	1500	33461 TAPE MOUNTED ON 15.24[.600] CENTERS	2-33461-2
2 3	6	100	LOOSE PIECE	33461
APPROVALS	FINISH	QTY	PACKAGE TYPE	PART NO.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION	TOOLING ASSISTANCE CENTER
TOOLING INFORMATION	1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142
MAX RECOMMENDED OPERATING TEMPERATURE: 170°C [338°F] MAX	
VOLTAGE RATING: NOT APPLICABLE	
WIRE CROSS SECTIONAL AREA RANGE, 6.6-10.5mm²[13,100-20,800] CIR MILS SOLID OR STRANDED	

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± 0.127[.005]
4 PLC ± -	4 ANGLES ± -
MATERIAL COPPER PER ASTM B-152 ANNEALED	FINISH -

DWN TA BRINKMAN 3-24-93	TE Connectivity	NAME	TERMINAL, RING TONGUE, SOLISTRAND 8 AWG
CHK DA PATTERSON 3-24-93		SIZE	A2
APVD JL MECKLEY 3-24-93		CAGE CODE	00779
PRODUCT SPEC		DRAWING NO	C=33461
APPLICATION SPEC	WEIGHT	-	RESTRICTED TO
CUSTOMER DRAWING	SCALE	8:1	SHEET 1 OF 1
	REV	T4	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-33461-2](#)