

	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE		COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△						△					
△						△					

APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C	STORAGE TEMPERATURE RANGE	- °C TO - °C
	VOLTAGE		OPERATING HUMIDITY RANGE	- % TO - %
	CURRENT		APPLICABLE CABLE	MAX φ 9.4

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
------	-------------	--------------	----	----

CONSTRUCTION

GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	<input type="radio"/>	<input type="radio"/>
MARKING	VISUALLY AND BY MEASURING INSTRUMENT.		<input type="radio"/>	<input type="radio"/>

MECHANICAL CHARACTERISTICS

VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, - m/s ² AT 2 h, FOR 3 DIRECTIONS.	NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	<input type="radio"/>	-
SHOCK	490 m/s ² DIRECTIONS OF PULSE 11 ms AT 3 TIME FOR 6 DIRECTION.		<input type="radio"/>	-

ENVIRONMENTAL CHARACTERISTICS

CORROSION SALT MIST	EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.	NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	<input type="radio"/>	-
---------------------	---	---	-----------------------	---

REMARKS

REMARKS	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
	<i>A. Kato</i> 99.11.4	<i>A. Kato</i> 99.11.4	<i>J. Esami</i> 99.11.5	<i>H. Miura</i> 99.11.5	

Unless otherwise specified, refer to JIS C 5402.
 Note QT:Qualification Test AT:Assurance Test ○:Applicable Test

HRS HIROSE ELECTRIC CO., LTD.	SPECIFICATION SHEET	PART NO. DX-50-CV1
CODE NO.(OLD) CL	DRAWING NO. ELC4-040136	CODE NO. CL230-0057-6
		1/1

TO
Q1