









Hand tools

Crimping tools

Crimping tools

Terminals and parts model number in alphabetical order	Hand tools						Hand tools		Extraction and Insertion tools	
	for chain terminals	for loose piece terminals					for loose piece terminals		Extraction tool	Insertion tool
	YRS series	YC series	YRM series	YRF series	YRK series	YRK-EX series				
										
	Dimensions: (W L) 59 224 mm	Dimensions: (W L) 70 296 mm	Dimensions: (W L) 59 224 mm	Dimensions: (W L) 70 295 mm 80 305 mm	Dimensions: (W L D) 75 314 25 mm	Dimensions: (W L D) 75 314 25 mm				
	Crimping tools It is the manual tool that is convenient to terminate very small quantity of contacts for prototype or maintenance. It is composed of two crimping dies for the conductor and insulation, and can be crimp easily. YRK and YRK-EX can be used for mass-production. Note: (1) These tools are for prototype tooling or repair. (2) YC tool has two crimping sections (A and B). YRS tool has also two crimping sections by inverting upper dies. Be sure to check applicable wires before use. Since the dies are fixed, the crimping height cannot be adjusted. Therefore, some of the applicable wires described in this catalog may not be crimped properly. Before use, check for proper crimping (such as tensile strength, terminal/contact deformation). (3) These tools are not applicable to 2-wire crimping. (4) When hand crimping board-in terminals (SAN, SCN, SDN, SGN, SIN, SJN, SZN), care should be taken not to contaminate the solder tails of the terminals, as with greasy or oily fingers. If a solder problem arises, some cleaning of the tips of the terminal is advisable. (5) WC and JUC hand tools are provided by J.S.T.(U.K.) LTD. and contact them about the details of these hand tools.									
	YRS series	YC series	YRM series	YRF series	YRK · YRK-EX series		WC & JUC series JUK's Hand Tools	Terminal in loose form model No.		
JK-SP2**/JK-SS2**	YRS-370	-	-	-	-	-	-	-	KEJ-0.7 for plug, KEJ-0.4 for socket	-
J-SP1**/J-SS1**	YRS-440	YC-440	-	-	-	-	-	J-BP/BS1**	DEJ-0.3	-
J-SP2**/J-SS2**	YRS-330	-	-	-	-	-	-	-	DEJ-0.3	-
LFO-1.0-250N	-	-	-	-	-	-	JUCS-FO	-	-	-
LFO-2.5-250N	-	-	-	-	-	-	JUCS-FO	-	-	-
MD-SP12**	YRS-470	-	-	-	-	-	-	-	MEJ-06	-
MD-SP22**	YRS-460	-	-	-	-	-	-	-	MEJ-06	-
RA-SC1290	YRS-231	-	YRM-232 YRM-233	-	-	-	-	RA-BC12**	EJ-RA	-
RF-SC22**	-	-	YRM-230	-	-	-	-	RF-BC22**	-	-
RPJ-SP2331	YRS-331	-	-	-	-	-	-	-	EJ-RPJ	-
RPJ-SS2331	-	-	-	-	-	-	-	-	-	-
SAA-21(T)-**	-	YC-141	-	-	-	-	-	LAA-21(T)-**	-	-
SAA-50(T)-**	-	YC-182	-	-	-	-	-	LAA-50(T)-**	-	-
SAA-51(T)-**	-	YC-142	-	-	-	-	-	LAA-51(T)-**	-	-
SAB-51(T)-**	-	YC-142	-	-	-	-	-	LAB-51(T)-**	-	-
SACH-003G-P0.2	YRS-1190	-	-	-	-	-	-	-	-	-
SAGH-002GU-P0.3	YRS-858	-	-	-	-	-	-	-	-	-
SAN-002T-0.8A	YRS-220	-	-	-	-	-	-	-	EJ-PH	-
SAN-002T-0.8K	-	-	-	-	-	-	-	-	-	-
SBH-001T-P0.5	-	YC-670R	-	-	-	-	WC-670	BBH-001T-P0.5	-	-
SBHL-002T-P0.5	YRS-857	-	-	-	-	-	-	-	-	-
SBHM-001T-P0.5	-	YC-670R	-	-	-	-	-	BBHM-001T-P0.5	EJ-BHMR	-
SBHS-002T-P0.5A	YRS-852	-	-	-	-	-	-	-	EJ-BHS2	-
SBHS-002T-P0.5A	-	-	-	-	-	-	-	-	EJ-BHS2	-
SBHSM-002T-P0.5	YRS-854	-	-	-	-	-	-	-	EJ-BHSW	-
SBHT-002T-P0.5	YRS-856 YRS-857	-	-	-	-	-	-	-	EJ-BHT	-
SBN-001T-1.0	YRS-170	YC-170R	-	-	-	-	-	BBN-001T-1.0	-	-
SCN-001T-1.0K	YRS-191	YC-191R	-	-	-	-	WC-191	BCN-001T-1.0K	-	-
SCN-001T-P1.0	-	-	-	-	-	-	-	BCN-001T-P1.0	-	-
SCS-41T-2.3	-	-	-	-	-	-	-	-	CSJ-23	-
SCSH-002T-P0.2N	YRS-1350	-	-	-	-	-	-	-	-	-

Note: Contact JST for wire range.

Crimping tools

Terminals and parts model number in alphabetical order	Hand tools						Hand tools		Extraction and Insertion tools	
	for chain terminals	for loose piece terminals				for loose piece terminals		Extraction tool	Insertion tool	
		YRS series	YC series	YRM series	YRF series	YRK · YRK-EX series	WC & JUC series JUK's Hand Tools			Terminal in loose form model No.
SCSN-41T-P2.3	-	-	-	-	-	-	-	-	EJ-CSN	-
SCZH-002T-P0.5	YRS-492	-	-	-	-	-	-	-	-	-
SDACP-002T-M0.9	YRS-1530 YRS-1531	-	-	-	-	-	-	-	-	-
SDF-01T-1.0A	-	YC-045	-	-	-	-	-	LDF-01T-1.0A	-	-
SDF-01T-1.3AS	-	-	-	-	-	-	-	LDF-01T-1.3AS	-	-
SDN-21T-P1.5	-	YC-600R	-	-	-	-	-	BDN-21T-P1.5	-	-
SDY-01T-P1.6ASV	-	YC-525R	-	-	-	-	-	BDY-01T-P1.6ASV	SLJ-1.4	-
SEH-001T-P0.6	YRS-260	YC-260R	-	-	-	-	WC-260	BEH-001T-P0.6	EJ-PH	-
SEH-001T-P0.6L	-	-	-	-	-	-	-	-	EJ-PH	-
SEH-002T-P0.6L	-	-	-	-	-	-	-	-	EJ-PH	-
SEH-003T-P0.6L	-	-	-	-	-	-	-	-	EJ-PH	-
SF1F-01GC-P0.6	-	-	-	-	-	YRK-1230	-	-	-	-
SF1M-01GC-M0.6A	-	-	-	-	-	-	-	-	-	-
SF1F-002T(GC)-P0.6	-	-	-	-	-	YRK-1220	-	-	FJ-JFAJ1100	-
SF1M-002T(GC)-M0.6A	-	-	-	-	-	-	-	-	-	-
SF1F-21T(GC)-P0.6	-	-	-	-	-	YRK-1210	-	-	FJ-JFAJ1100	-
SF1M-21T(GC)-M0.6A	-	-	-	-	-	-	-	-	-	-
SF3F-002(*)-P2.0	-	-	-	YRF-882	YRK-8821	-	-	BF3F-002(*)-P2.0 BF3M-002(*)-M2.0N	FJ-JFAJ3	-
SF3M-002(*)-M2.0N	-	-	-	-	-	-	-	-	-	-
SF3F-01(*)-P2.0	-	-	-	YRF-881	YRK-8811	-	-	BF3F-01(*)-P2.0 BF3M-01(*)-M2.0N	FJ-JFAJ3	-
BF3M-002(*)-M2.0N	-	-	-	-	-	-	-	-	-	-
SF3F-41(*)-P2.0	-	-	-	YRF-880	YRK-8801	-	-	LF3F-41(*)-P2.0 LF3M-41(*)-M2.0N	FJ-JFAJ3	-
SF3M-41(*)-M2.0N	-	-	-	-	-	-	-	-	-	-
SF3F-71(*)-P2.0	-	-	-	YRF-1070	YRK-1071	-	-	BF3F-71(*)-P2.0 BF3M-71(*)-M2.0N	FJ-JFAJ3	-
SF3M-71(*)-M2.0N	-	-	-	-	-	-	-	-	-	-
SFO-41(T)-187N(-8)	-	YC-271	-	-	-	-	-	LFO-41(T)-187N	-	-
SFO-61(T)-250A	-	YC-270	-	-	-	-	-	LFO-61(T)-250A	-	-
SFPS-61T-250	-	YC-272	-	-	-	-	-	LFPS-61(T)-250	-	-
SFT-61T-250N	-	YC-510	-	-	-	-	-	LFT-61T-250N	-	-
SGF-41(T)-4	-	YC-055	-	-	-	-	-	LGF-41(T)-4	-	-
SGF-51(T)-5	-	YC-065	-	-	-	-	-	LGF-51(T)-5 LGF-51(T)-5A	-	-
SGHD-002GA-P0.2	YRS-1590	-	-	-	-	-	-	-	-	-
SGM-51T-5	-	YC-056	-	-	-	-	-	LGM-51T-5	-	-
SGVH-002T-P0.2	YRS-1590	-	-	-	-	-	-	-	-	-
SHCM-A03T-P025	YRS-960	-	-	-	-	-	WC-SHCM-A03	-	-	-
SHF-001T-0.8BS	YRS-122	YC-122R	-	-	-	-	WC-122	BHF-001T-0.8BS	EJ-SMP (Note1)	-
SHF-002T-0.8BS	YRS-300	-	-	-	-	-	-	-	EJ-SMP (Note1)	-
SHIF-01T-P0.5	-	YC-985R	-	-	-	-	-	-	EJ-HILP	-
SHIF-21T-P0.5	-	YC-995R	-	-	-	-	-	-	EJ-HILP	-
SHIM-01T-P0.5	-	YC-985R	-	-	-	-	-	-	EJ-HILR	-
SHIM-21T-P0.5	-	YC-995R	-	-	-	-	-	-	EJ-HILR	-
SHR-001T-P0.6	YRS-580	YC-580R	-	-	-	-	-	BHR-001T-P0.6	-	-
SHYVF-21T-M0.5	-	-	-	-	-	-	-	-	EJ-BNI	-
SHYVF-41T-M0.5	-	-	-	-	-	-	-	-	EJ-BNI	-
SIM-01(T)-110A	-	YC-054	-	-	-	-	-	LIM-01(T)-110A	-	-
SIM-1.0-250D/N	-	-	-	-	-	-	JUCS-IM	-	-	-
SIM-2.5-250D/N	-	-	-	-	-	-	JUCS-IM	-	-	-
SIM-41(T)-110B	-	YC-067	-	-	-	-	-	LIM-41(T)-110B	-	-
SIM-51(T)-250N	-	YC-321	-	-	-	-	-	LIM-51(T)-250N	-	-

Note 1: Please use EJ-SMP as an extraction tool when using the combination with SM connector 18-circuit housing.
 2: Contact JST for wire range.

Crimping tools

Terminals and parts model number in alphabetical order	Hand tools						Hand tools		Extraction and Insertion tools	
	for chain terminals	for loose piece terminals				for loose piece terminals		Extraction tool	Insertion tool	
		YRS series	YC series	YRM series	YRF series	YRK · YRK-EX series	WC & JUC series JUK's Hand Tools			Terminal in loose form model No.
SIN-001T-1.2	YRS-034	-	-	-	-	-	-	-	-	
SIN-002T-1.0S	YRS-035	-	-	-	-	-	-	-	-	
SIN-01T-1.2	-	YC-340R	-	-	-	-	-	LIN-01T-1.2	-	
SIN-01T-1.8	-	YC-032	-	-	-	-	-	LIN-01T-1.8	-	
SIN-01T-1.8N	-	YC-032	-	-	-	-	-	LIN-01T-1.8N	-	
SIN-21T-1.8	-	YC-350	-	-	-	-	-	LIN-21T-1.8	-	
SIN-21T-1.8S	-	YC-570 YC-571	-	-	-	-	-	LIN-21T-1.8S	-	
SIN-61T-2.6S	-	YC-560	-	-	-	-	-	LIN-61T-2.6S	-	
SIN-81T-3.6S	-	YC-940	-	-	-	-	-	LIN-81T-3.6S	-	
SIN-91T-4.7S	-	-	-	-	-	YRK-1630	-	-	-	
SJ2F-002GF-P1.0 SJ2M-002GF-M1.0N	YRS-8851	-	-	-	-	YRK-8851	-	-	EJ-JFAJ2N	
SJ2F-01GF-P1.0 SJ2M-01GF-M1.0N SJ2M-01GF-M1.0S	YRS-8861	-	-	-	-	YRK-8861	-	-	EJ-JFAJ2N	
SJ2F-21GF-P1.0 SJ2M-21GF-M1.0N	-	-	-	YRF-1120	YRK-1120	-	-	LJ2F-21GF-P1.0 LJ2M-21GF-M1.0N	EJ-JFAJ2N	
SJ3F-002GF-P1.8	-	-	-	YRF-882	-	-	-	-	-	
SJ3F-01GF-P1.8	-	-	-	YRF-881	-	-	-	-	-	
SJ3F-41GF-P1.8	-	-	-	YRF-880	-	-	-	-	-	
SJ4F-71GF-M3.0	-	-	-	YRF-1130	-	-	-	BJ4F-71GF-M3.0	EJ-JFAJ4	
SJ4F-81GF-M3.0	-	-	-	YRF-1370	-	-	-	BJ4F-81GF-M3.0	EJ-JFAJ4	
SJ5F-71GF-M6.5 SJ5M-71GF-M6.5	-	-	-	YRF-888	-	-	-	BJ5F-71GF-M6.5 BJ5M-71GF-M6.5	EJ-JFAJ5	
SJ5F-81GF-M6.5 SJ5M-81GF-M6.5	-	-	-	YRF-889	-	-	-	LJ5F-81GF-M6.5 LJ5M-81GF-M6.5	EJ-JFAJ5	
SJ5F-91GF-M6.5 SJ5M-91GF-M6.5	-	-	-	-	-	-	-	LJ5F-91GF-M6.5 LJ5M-91GF-M6.5	EJ-JFAJ5	
SJFPS-81T-M1.0	-	-	-	YRF-1610	-	-	-	-	-	
SJN-001PT-0.9	YRS-1181	-	-	-	-	-	-	-	-	
SJN-002PT-0.9	YRS-036	-	-	-	-	-	-	-	-	
SJWPSR-21T-P1.0 SJWPST-21T-M1.0N	-	-	-	-	-	-	-	-	EJ-JWPS-RT	
SLC-21T-2.0	-	YC-310	-	-	-	-	WC-310	LLC-21T-2.0	-	
SLC-001T-P2.0	-	-	-	-	-	-	-	-	EJ-LCL	
SLC-02T-P2.0	-	-	-	-	-	-	-	-	EJ-LCL	
SLF-01T-P1.3E SLM-01T-P1.3E	-	YC-202	YRM-201	-	-	-	WC-202	LLF/M-01T-P1.3E	LEJ-13 LIT-2013	
SLF-41T-P1.3E SLM-41T-P1.3E	-	YC-203	-	-	-	-	WC-203	LLF/M-41T-P1.3E	LEJ-13	
SMF-01T-1.0	-	YC-081	-	-	-	-	-	LMF-01T-1.0	-	
SMF-01T-1.3	-	YC-082	-	-	-	-	-	LMF-01T-1.3	-	
SMM-003T-P0.5	YRS-800	-	-	-	-	-	WC-800	-	-	
SMR-001T-0.6	YRS-580	YC-580R	-	-	-	-	-	BMR-001T-0.6	-	
SOM-21(T)-187	-	YC-680	-	-	-	-	-	LOM-21(T)-187	-	
SOM-51(T)-250	-	YC-066	-	-	-	-	WC-066	LOM-51(T)-250	-	
SOTZP-002GD-P0.18	-	-	-	-	-	-	-	-	EJ-OTZS	

Note: Contact JST for wire range.

Crimping tools

Terminals and parts model number in alphabetical order	Hand tools						Hand tools		Extraction and Insertion tools	
	for chain terminals	for loose piece terminals				for loose piece terminals		Extraction tool	Insertion tool	
		YRS series	YC series	YRM series	YRF series	YRK · YRK-EX series	WC & JUC series JUK's Hand Tools			Terminal in loose form model No.
SPA-001T-P0.5	-	YC-610R YC-611R	-	-	-	-	-	BPA-001T-P0.5	EJ-PH	-
SPAL-001T-P0.5	-	YC-610R YC-611R	-	-	-	-	-	BPAL-001T-P0.5	EJ-PAL	-
SPAL-002T-P0.5	YRS-1340	-	-	-	-	-	-	-	EJ-PAL	-
SPB-1.0-250N-S	-	-	-	-	-	-	JUCS-PB	-	-	-
SPB-2.5-250N-S	-	-	-	-	-	-	JUCS-PB	-	-	-
SPBD-001T-P0.5	-	YC-610R	-	-	-	-	-	-	-	-
SPBD-002T-P0.5	-	YC-611R	-	-	-	-	-	-	-	-
SPF-01T-2.5C	-	YC-043R	-	-	-	-	-	LPF-01T-2.5C	-	-
SPH-001T-P0.5L	YRS-245	-	-	-	-	-	-	-	-	-
SPH-002T-P0.5L	YRS-241	-	-	-	-	-	-	-	EJ-PH	-
SPH-002T-P0.5S	YRS-240	-	YRM-240	-	-	-	WC-240	BPH-002T-P0.5S	EJ-PH	-
SPH-004T-P0.5S	YRS-243	-	-	-	-	-	-	-	EJ-PH	-
SPHD-001T-P0.5	-	YC-610R YC-611R	-	-	-	-	WC-610	BPHD-001T-P0.5	EJ-PHD-RB	-
SPHD-002T-P0.5	YRS-620	-	YRM-620	-	-	-	WC-620	BPHD-002T-P0.5	EJ-PHD-RB	-
SPID-001T-P0.5	YRS-1620	-	-	-	-	-	-	-	EJ-PID	-
SPLI-002T-P0.5	YRS-1410	-	-	-	-	-	-	-	-	-
SPND-001T-C0.5	YRS-1091	-	-	-	-	-	-	-	EJ-PND	-
SPND-002T-C0.5	YRS-1090	-	-	-	-	-	-	-	EJ-PND	-
SPNI-001T-P0.5	-	YC-610R YC-611R	-	-	-	-	-	-	-	-
SPNI-002T-P0.5	YRS-1340	-	-	-	-	-	-	-	-	-
SPS-01T-110	-	YC-740	-	-	-	-	WC-740	LPS-01T-110	-	-
SPS-01T-187(-8)	-	YC-730 YC-731	-	-	-	-	WC-730	LPS-01T-187(-8)	EJ-PS187	-
SPS-21T-205(-5)	-	YC-760	-	-	-	-	-	LPS-21T-205(-5)	-	-
SPS-21T-250	-	YC-780	-	-	-	-	WC-780	LPS-21T-250	EJ-PS250	-
SPS-21T-250S	-	YC-780	-	-	-	-	WC-780	LPS-21T-250S	EJ-PS250	-
SPS-21T-250R	-	YC-780	-	-	-	-	-	LPS-21T-250R	EJ-PS250	-
SPS-41T-110	-	YC-750 YC-751	-	-	-	-	WC-750	LPS-41T-110	-	-
SPS-51T-187(-8)	-	YC-710 YC-711	-	-	-	-	WC-710	LPS-51T-187(-8)	EJ-PS187	-
SPS-51T-205	-	YC-770 YC-771	-	-	-	-	-	LPS-51T-205	-	-
SPS-61T-250	-	YC-720	-	-	-	-	WC-720	LPS-61T-250	EJ-PS250	-
SPS-61T-250S	-	YC-720	-	-	-	-	-	LPS-61T-250S	EJ-PS250	-
SPS-61T-250R	-	YC-721	-	-	-	-	-	LPS-61T-250R	EJ-PS250	-
SPS-91T-250	-	-	-	YRF-790	-	-	-	BPS-91T-250	EJ-PS250	-
SPS-91T-250S	-	-	-	YRF-790	-	-	-	BPS-91T-250S	EJ-PS250	-
SPS-91T-250R	-	-	-	YRF-791	-	-	-	BPS-91T-250R	EJ-PS250	-
SPSI-001T-M1.1	-	YC-335R	-	-	-	-	-	-	EJ-PSIP	-
SPSM-001T-M1.1	-	YC-335R	-	-	-	-	-	-	EJ-PSIR	-
SPSI-41T-M1.1	-	YC-225R	-	-	-	-	-	-	EJ-PSIP	-
SPSM-41T-M1.1	-	YC-226R	-	-	-	-	-	-	EJ-PSIR	-
SPUD-001T-P0.5	YRS-1320	-	-	-	-	-	-	-	EJ-PUD	-
SPUD-002T-P0.5	YRS-1520	-	-	-	-	-	-	-	EJ-PUD	-

Note: Contact JST for wire range.

Crimping tools

Terminals and parts model number in alphabetical order	Hand tools						Hand tools		Extraction and Insertion tools	
	for chain terminals	for loose piece terminals				for loose piece terminals		Extraction tool	Insertion tool	
		YRS series	YC series	YRM series	YRF series	YRK · YRK-EX series	WC & JUC series JUK's Hand Tools			Terminal in loose form model No.
SPXA-001T-P0.6	-	-	-	-	-	-	-	-	EJ-PXA	-
SRA-20(T)-**	-	YC-181	-	-	-	-	-	LRA-20(T)-**	-	-
SRA-21(T)-**	-	YC-141	-	-	-	-	-	LRA-21(T)-**	-	-
SRA-50(T)-**	-	YC-182	-	-	-	-	-	LRA-50(T)-**	-	-
SRA-51(T)-**	-	YC-142	-	-	-	-	-	LRA-51(T)-**	-	-
SRB-1.0(-)	-	-	-	-	-	-	JUCS-RB/RT	-	-	-
SRB-2.5(-)	-	-	-	-	-	-	JUCS-RB/RT	-	-	-
SRB-51(T)-**	-	YC-142	-	-	-	-	-	LRB-51(T)-**	-	-
SRC-01(T)-**	-	YC-033	-	-	-	-	-	LRC-01(T)-**	-	-
SRC-50(T)-**	-	YC-183	-	-	-	-	-	LRC-50(T)-**	-	-
SRC-51(T)-**	-	YC-142	-	-	-	-	-	LRC-51(T)-**	-	-
SRF-51(T)-**	-	YC-142	-	-	-	-	-	LRF-51(T)-**	-	-
SRFCP-002GG-M0.9	YRS-1530 YRS-1531	-	-	-	-	-	-	-	FJ-RFC-P	-
SRFF-01GG-S0.9	-	-	-	-	-	-	-	-	EJ-RFC-R	-
SRFF-61GG-S0.9	-	-	-	YRF-1450	-	-	-	-	EJ-RFC-R	-
SRFM-01GG-S0.9	-	-	-	-	-	-	-	-	EJ-RPZ	-
SRFM-61GG-S0.9	-	-	-	YRF-1450	-	-	-	-	EJ-RPZ	-
SRICM-61GG-S0.6 SRICM-61T-S0.6	-	YC-840R	-	-	-	-	-	-	-	-
SRT-1.0(-)	-	-	-	-	-	-	JUCS-RB/RT	-	-	-
SRT-2.5(-)	-	-	-	-	-	-	JUCS-RB/RT	-	-	-
SRT-51T-**	-	YC-143R	-	-	-	-	-	LRT-51T-**	-	-
SRWF-01GG-M0.6 SRWF-01T-M0.6 SRWM-01GG-S0.6	-	-	-	-	-	-	-	-	EJ-RPZ	-
SRWF-21GG-M0.6 SRWM-21GG-S0.6	-	-	-	-	-	-	-	-	EJ-RPZ	-
SRWF-61GG-M0.6 SRWF-61T-M0.6 SRWM-61GG-S0.6	-	YC-840R	-	-	-	-	-	BRWF-61GG-M0.6 BRWM-61GG-S0.6	EJ-RPZ	-
SSFH-001T-P0.5	YRS-1580 YRS-1581	-	-	-	-	-	-	-	FJ-SFH	-
SSFH-002T-P0.5	YRS-1490	-	-	-	-	-	-	-	EJ-SFH	-
SSH-003T-P0.2-H	YRS-859	-	-	-	-	-	WC-SH2832	-	-	-
SSH-003GA-P0.2	YRS-859	-	-	-	-	-	WC-SH2832	-	-	-
SSHJ-003T-P0.2	YRS-859	-	-	-	-	-	-	-	-	-
SSHL-002T-P0.2	YRS-1590	-	-	-	-	-	WC-GH2630	-	-	-
SSHL-003T-P0.2	YRS-859	-	-	-	-	-	WC-SH2832	-	-	-
SSHL-003GA1-P0.2	YRS-859	-	-	-	-	-	WC-SH2832	-	-	-
SSF-01T-P1.4 SSM-01T-P1.4	-	YC-500	-	-	-	-	-	BSF/M-01T-P1.4	SLJ-1.4	ITBL-08V
SSF-21T-P1.4 SSM-21T-P1.4	-	YC-550	-	-	-	-	WC-550	BSF/M-21T-P1.4	SLJ-1.4	-
STI-01(T)-110N	-	YC-041	-	-	-	-	-	LTI-01(T)-110N	-	-
STI-1.0-250D/N	-	-	-	-	-	-	JUCS-TI	-	-	-
STI-2.5-250D/N	-	-	-	-	-	-	JUCS-TI	-	-	-
STI-41(T)-110N	-	YC-063	-	-	-	-	-	LTI-41(T)-110N	-	-
STI-51(T)-250N	-	YC-322	-	-	-	-	-	LTI-51(T)-250N	-	-
STO-01(T)-110N(-8)	-	YC-041	-	-	-	-	-	LTO-01(T)-110N(-8)	-	-
STO-01(T)-187N(-8)	-	YC-042	-	-	-	-	-	LTO-01(T)-187N(-8)	-	-

Note: Contact JST for wire range.

Crimping tools

Terminals and parts model number in alphabetical order	Hand tools						Hand tools		Extraction and Insertion tools	
	for chain terminals	for loose piece terminals				for loose piece terminals		Extraction tool	Insertion tool	
	YRS series	YC series	YRM series	YRF series	YRK · YRK-EX series	WC & JUC series JUC's Hand Tools	Terminal in loose form model No.			
STO-0.25-110N	-	YC-810	-	-	-	-	-	-	-	
STO-0.5-110N	-	YC-820	-	-	-	-	JUCS-05110	-	-	
STO-1.0-110N	-	-	-	-	-	-	JUCS-2.8/4.8	-	-	
STO-1.0-187N	-	-	-	-	-	-	JUCS-2.8/4.8	-	-	
STO-1.0-250N	-	-	-	-	-	-	JUCS-6.3	-	-	
STO-2.5-250N	-	-	-	-	-	-	JUCS-6.3	-	-	
STO-21(T)-205N(-5)	-	YC-053	-	-	-	-	-	LTO-21(T)-205N	-	
STO-21(T)-250N	-	YC-102	-	-	-	-	-	LTO-21(T)-250N	-	
STO-41(T)-110N(-8)	-	YC-062	-	-	-	-	-	LTO-41(T)-110N(-8)	-	
STO-41(T)-187N(-8)	-	YC-051	-	-	-	-	-	LTO-41(T)-187N(-8)	-	
STO-41T-187S	-	YC-064	-	-	-	-	-	LTO-41T-187S	EJ-187S	
STO-61(T)-250N	-	YC-047	-	-	-	-	-	LTO-61(T)-250N	-	
STO-81(T)-250N	-	YC-280	-	YRF-280	-	-	-	LTO-81(T)-250N	-	
STS-002GG-P0.6 STSD-002GG-P0.6	YRS-1360	-	-	-	-	-	-	-	EJ-TSD	
SVA-41T-P1.1	-	YC-450	-	-	-	-	-	BVA-41T-P1.1	-	
SVF-01T-1.5A	-	YC-044	-	-	-	-	-	LVF-01T-1.5A	-	
SVF-01T-1.5N	-	YC-151	-	-	-	-	-	LVF-01T-1.5N	EJ-SV	
SVF-01T-2.36N	-	YC-152	-	-	-	-	-	LVF-01T-2.36N	EJ-LV	
SVF-42T-P2.0	-	YC-592	-	-	-	-	WC-592	BVF-42T-P2.0	VLJ-20	
SVM-42T-P2.0	-	YC-593	-	-	-	-	WC-592	BVM-42T-P2.0	VLJ-20	
SVF-61T-P0.2 SVM-61T-P0.2	-	YC-590	-	YRF-590	-	-	WC-590	BVF/M-61T-P2.0	VLJ-20	
SVF-81T-P0.2 SVM-81T-P0.2	-	-	-	YRF-591	-	-	WC-591	BVF/M-81T-P2.0	VLJ-20	
SVH-21T-P1.1	-	YC-160R YC-161R YC-164R	YRM-160 - YRM-164	-	-	-	WC-160	BVH-21T-(P)1.1	EJ-NV	
SVH-41T-P1.1	-	YC-930R YC-931R	-	-	-	-	WC-930	BVH-41T-P1.1	EJ-NV	
SVT-41T-P1.1	-	YC-630	-	-	-	-	-	BVT-41T-P1.1	EJ-VT	
SVU-21T-P0.6	-	YC-990R	-	-	-	-	-	BVU-21T-P0.6	EJ-VU4	
SVYF-61T-P0.5A	-	-	-	YRF-536	-	-	-	-	-	
SWPJT-21T-P0.5 SWPJT-21T-P0.5A	-	-	-	-	-	-	-	-	EJ-WPJ	
SWPJR-21T-M0.5	-	-	-	-	-	-	-	-	EJ-WPJ	
SWPKP-21T-0.6 SWPKR-21T-0.6	-	-	-	YRF-1051 YRF-1050	-	-	-	BWPKP-21T-0.6 BWPKR-21T-0.6	-	
SWPR-001T-P025 SWPT-001T-P025	YRS-980	-	-	-	-	-	WC-JWPF	-	EJ-JWPF	
SXA-01T-P0.6 SXA-001T-P0.6	YRS-701	YC-701R	-	-	-	-	WC-700M	BXA-01T-P0.6 BXA-001T-P0.6	EJ-XAG,EJ-XMP EJ-XMP, EJ-XMR	
SXA-001T-P0.6L	YRS-691	-	-	-	-	-	WC-691	-	-	
SXAM-01T-P0.6 SXAM-001T-P0.6	YRS-701	YC-701R	-	-	-	-	WC-700M	BXAM-01T-P0.6 BXAM-001T-P0.6	EJ-XAW EJ-XAW	
SXF-01T-P0.7 SXF-41T-P0.7	-	YC-251 YC-252	-	-	-	-	-	BXF-01T-(P)0.7 BXF-41T-(P)0.7	LEJ-7 LEJ-7	

Note: Contact JST for wire range.

Crimping tools

Terminals and parts model number in alphabetical order	Hand tools						Hand tools		Extraction and Insertion tools	
	for chain terminals	for loose piece terminals				for loose piece terminals		Extraction tool	Insertion tool	
	YRS series	YC series	YRM series	YRF series	YRK · YRK-EX series	WC & JUC series JUK's Hand Tools	Terminal in loose form model No.			
SXH-001T-P0.6	YRS-110	YC-110R YC-111R	-	-	-	WC-110	BXH-001T-P0.6	XJ-06	-	
SXH-001T-P0.6N	-	-	-	-	-	-	-	XJ-06	-	
SXH-002T-P0.6	YRS-480	-	-	-	-	-	-	XJ-06	-	
SXM-01T-P0.6	YRS-701	YC-701R	-	-	-	-	BXM-01T-P0.6	EJ-XAG,EJ-XMP	-	
SXM-001T-P0.6	YRS-692	YC-692R	-	-	-	-	BXM-001T-P0.6	EJ-XMP, EJ-XMR	IT-XA	
SXNI-001T-P0.6	YRS-1380	-	-	-	-	-	-	-	-	
SXNI-003T-P0.6	YRS-1390	-	-	-	-	-	-	-	-	
SYF-001T-P0.6	YRS-125	-	-	-	-	-	-	-	-	
SYF-01T-P0.5A	-	YC-520	-	-	-	WC-520	BYF-01T-P0.5A	YLJ-0.5	-	
SYM-01T-P0.5A	-	-	-	-	-	-	BYM-01T-P0.5A	-	-	
SYF-41T-P0.5A	-	YC-530	-	-	-	WC-530	BYF-41T-P0.5A	YLJ-0.5	-	
SYM-41T-P0.5A	-	-	-	-	-	-	BYM-41T-P0.5A	-	-	
SYF-61T-P0.5A	-	-	-	YRF-536	-	-	-	-	-	
SYM-001T-P0.6	YRS-121	YC-121R	-	-	-	WC-121	BYM-001T-P0.6	SMJ-06	-	
SYM-01T-P0.7	-	YC-251	-	-	-	-	BYM-01T-(P)0.7	LEJ-7	-	
SYM-41T-P0.7	-	YC-252	-	-	-	-	BYM-41T-(P)0.7	LEJ-7	-	
SZE-002T-P0.3	YRS-1460	-	-	-	-	-	-	-	-	
SZE-003T-P0.3	YRS-1330	-	-	-	-	-	-	-	-	
SZF-01T-P0.7	-	YC-390R	-	-	-	-	BZF-01T-(P)07	ZLJ-0.7S	-	
SZM-01T-P0.7	-	-	-	-	-	-	BZM-01T-(P)0.7	-	-	
SZF-41T-P0.7	-	YC-380R	-	-	-	-	BZF-41T-(P)07	ZLJ-0.7S	-	
SZM-41T-P0.7	-	-	-	-	-	-	BZM-41T-(P)0.7	-	-	
SZH-002T-P0.5	YRS-491	-	-	-	-	WC-491	-	-	-	
SZH-003T-P0.5	YRS-490	-	-	-	-	WC-490	-	-	-	
SZN-002T-P0.7K	YRS-541	-	-	-	-	-	-	-	-	
SZN-003T-P0.7K	YRS-540	-	-	-	-	-	-	-	-	
SZPD-002T-P0.3	YRS-1460	-	-	-	-	-	-	-	-	

Note : Contact JST for wire range.