



NC5MXX-HD-D

Heavy duty male 5 pole XLR cable connector for outdoor use.

Features & Benefits

- Dust and water ingress sealing according to IP67 in combination with HD cable connector NC5FXX-HD*
- Rubber sealing jacket protects against water ingress and mechanical shock
- Gold contacts

Technical Information

Product	
Title	NC5MXX-HD-D
Connection Type	XLR
Gender	male

Electrical	
Capacitance between contacts	≤ 7 pF
Contact resistance	≤ 3 m Ω
Dielectric strength	1.5 kVdc
Insulation resistance	> 10 G Ω (initial), > 1 G Ω (after damp heat test)
Number of electrical contacts	5
Rated current per contact	7.5 A
Rated voltage	< 50 V ac

Mechanical	
Cable O.D.	6.0 - 8.0 mm
Insertion force	≤ 20 N
Withdrawal force	≤ 20 N
Lifetime	1000 mating cycles
Wiresize	max. 1.0 mm ²
Wiresize	max. 18 AWG
Wiring	Solder contacts
Locking device	Latch lock

Material	
Boot	PA / PU
Contact plating	0.2 µm Au hard alloy over 2 µm Ni
Contacts	Brass (CuZn39Pb3)
Insert	Polyamide (PA 66)
Locking element	Zinc diecast (ZnAl4Cu1) / Ck 67 (spring)
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	Nickel
Strain relief	Polyacetal (POM)
Sealing jacket	EPDM

Environmental	
Flammability	UL 94 V-0
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C
Manufacturing Standard	IEC 61076-2-103

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Neutrik:](#)

[NC5MXX-HD-D](#)