

## Honeywell Sensing and Control

Search



### narrow your search

#### Products

- Controls Monitoring and Lighting (354)
- Machine Safety (1726)
- Sensors (7016)
- Switches (9676)

#### Technology

- Control and Instrumentation (1063)
- Electromechanical (9237)
- Microstructure (2298)
- Optical/Infrared (1077)
- Thick Film (1764)
- More...

### Need Help?

[Click here to contact us](#)

## 192-103LEV-A01 Discrete Thermistors

(Home : Products)



*Actual product appearance may vary.*

192 Series, Uni-Curve with bare leads and epoxy, 10,000 Ohm resistance,  $\pm 0,5$  °C [0.9 °F] tolerance, 25/85 BETA = 3974

[Sales & Service](#)
[Distributor Inventory](#)
[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

### Product Specifications

Availability	Global
Resistance	10,000 Ohm
Tolerance	$\pm 0,5$ °C [0.9 °F]
Accuracy	0 °C to 70 °C [32 °F to 158 °F]
Beta	3974
Operating Temperature	-60 °C to 150 °C [-76 °F to 302 °F]
Diameter	2,413 mm [0.095 in]
Termination Material	32 Gauge tinned copper, alloy 180
Lead Length	38,1 mm [1.50 in]
Time Constant in Air	15.0 s
Dissipation Constant	0,75 m/W°C
Series Name	192

[Terms & Conditions](#) | [Privacy Statement](#) | [Site Map](#)