





Features

- Heavy Industrial CE Approval
- 10 V/m EMI Protection
- ±0.25% Pressure Accuracy
- ±1.0% Total Error Band
- ±3°C Temperature Output Accuracy
- -10°C to +60°C Compensating Temperature
- -20°C to +85°C Operating Temperature

Applications

- Industrial Process Control and Monitoring
- Advanced HVAC Systems
- Refrigeration Systems
- Automotive Test Stands
- Off-Road Vehicles
- Pumps and Compressors
- Hydraulic/Pneumatic Systems
- Agriculture Equipment
- Energy Generation and Management
- Pool/Spa Pump Monitoring

MEAS M5600

Wireless Pressure Transducer

- Digital 24-bit ADC Output, I²C Protocol
- Bluetooth® 4.0 Wireless Connection
- CE Compliant with a Variety of Pressure Ports
- Compact and Battery Powered [CR2050]
- Optional Stainless Steel Snubber
- Weatherproof (IP66/IP67)
- FCC Certified
- Stainless Steel and Polycarbonate Enclosure
- Gage, Sealed, Compound
- iOS, Android™ and Windows® XP/7+ Compatible

The modular M5600 wireless pressure transducer from our Microfused line is enclosed in a stainless steel and polycarbonate housing. This high accuracy, 24-bit ADC digital output wireless transducer eliminates hard wiring and provides remote process control and monitoring via Bluetooth[®] 4.0 Wireless Communication. This series is suitable for measurement of liquid or gas pressure, even for difficult media such as contaminated water, steam, and mildly corrosive fluids.

The wetted material of the pressure port is made of 316L stainless steel and the transducer's durability is excellent with no o-rings or organics exposed to the pressure media. The M5600 is weatherproof and exceeds the latest heavy industrial CE requirements.

This product is geared to the OEM customer for mid to high volumes. TE stands ready to provide a custom design of the M5600 where the volume and application warrants. Additional configurations not listed are available. Please inquire for further information.

Standard Ranges

Range (psi)	Range (Bar)	Gage	Sealed	Compound
0 to 050	0 to 3.5	•		•
0 to 100	0 to 007	•		•
	0 to 010	•		•
0 to 200		•		•
0 to 300	0 to 020	•		•
0 to 500	0 to 035	•		•
0 to 01k	0 to 070	•	•	•
0 to 03k	0 to 200	•	•	•
0 to 05k	0 to 350	•	•	•
0 to 10k	0 to 700	•	•	•
0 to 15k	0 to 01k	•	•	•

Intermediate ranges available upon request.

Performance Specifications

Ambient Temperature: 25°C (unless otherwise specified) For custom configurations, consult factory.

Parameters	Min	Тур	Max	Units	Notes			
Supply Voltage	2.3	3	3.6	Vdc	Replaceable CR2050 battery			
Accuracy	-0.25		0.25	%F.S.	RSS of linearity, hysteresis, and repeatability			
Temperature Output Accuracy	-3		3	°C				
Output Protocol		Digital I ² C						
Resolution		24		Bit				
Endurance	1.00E+6			0~FS Cycles				
Stability	-0.25		0.25	%F.S./year				
Total Error Band	-1		1	%F.S.	@25°C over compensated range			
Proof Pressure	2X		20k psi	Rated				
Burst Pressure	3X		20k psi	Rated				
Compensated Temperature	-10		+60	°C				
Operating Temperature	-20		+85	°C	with battery			
Storage Temperature	-40		+120	°C	without battery			
Wireless Protocol	Bluetooth®	Bluetooth® 4.0 Wireless Connection or above						
Receiver Operating System	Android™	Android™ 4.3 or above, iOS 7 or above, Windows® XP/7 or above						
Signal Pairing Distance	Distance 65 feet							
Signal Transmission Distance	65 feet affe	65 feet affected by receiver antenna and blocking objects						
Battery Life	2 years typ	2 years typical CR2050 350mAH battery, 5 second transmission interval, room temperature						
Low Battery Warning	2.5Vdc, red	2.5Vdc, red battery symbol in app						
Weatherproof	IP66 & IP6	IP66 & IP67						
Pressure Port Material	17-4P Stair	17-4P Stainless Steel Port, 316L Stainless Steel Snubber						
Enclosure	Stainless S	Stainless Steel and Polycarbonate						
Shock	50g, 11mse	50g, 11msec Half Sine Shock per MIL-STD-202G, Method 213B, Condition A						
Vibration	±20g, MIL-	±20g, MIL-STD-810C, Procedure 514.2, Fig 514.2-2, Curve L						

Note:

CR2050 Battery not supplied by manufacturer.

Battery life depends on its capacity, operating temperature and signal transmission interval.

Some battery models offer high operating temperatures up to 125°C with nominal capacity 350mAH.

Temperature can impact battery capacity retention even if idle. Check battery specifications for more details.

Compliances

EN 55022 Emissions Class A & B

IEC 61000-4-2 Electrostatic Discharge Immunity (4kV contact/8kV air)


IEC 61000-4-3 Radiated, Radio-Frequency Electromagnetic Field Immunity (10V/m, 80M-1GHz); deviation <1.5%


RoHS

FCC

Bluetooth®

Dimensions [mm]





Code	Port	Dim B	Dim C Ref.	
2	1/4-19 BSPP	0.472 [11.94]	0.366 [9.3]	
3	G3/8 JIS B2351	0.540 [13.72]	0.366 [9.3]	
4	7/16-20UNF MALE SAE J1926-2 STRAIGHT THREAD O-RING BUNA-N 90SH-904	0.433 [11.0]	0.366 [9.3]	
5	1/4-18 NPT	0.600 [15.24]	0.366 [9.3]	
6	1/8-27 NPT	0.390 [9.91]	0.366 [9.3]	
В	G1/4 JIS B2351	0.472 [11.94]	0.366 [9.3]	
Е	1/4-19 BSPT	0.500 [12.7]	0.366 [9.3]	
F	1/4-19 BSPP FEMALE (without snubber)	0.771 [19.58]	0.366 [9.3]	
Р	7/16-20UNF FEMALE SAE J513 STRAIGHT THREAD WITH INTEGRAL VALVE DEPRESSOR	0.687 [17.5]	0.366 [9.3]	
Q	M10 x 1.0 mm ISO 6149-2	0.374 [9.5]	0.366 [9.3]	
N	7/16-20UNF FEMALE SAE J513 STRAIGHT THREAD	0.687 [17.5]	0.366 [9.3]	
S	M12 x 1.5 mm ISO 6149-2	0.433 [11.0]	0.366 [9.3]	
U	G/14 DIN 3852 FORM E GASKET DIN3869-14 NBR	0.472 [11.94]	0.445 [11.3]	
W	M20 x 1.5 mm ISO 6149-2	0.551 [14.0]	0.366 [9.3]	
G	M14 x 1.5 mm ISO 6149-2	0.433 [11.0]	0.366 [9.3]	

How to Operate

Please refer to the M5600/U5600 Installation Manual and M5600/U5600 Software Manual.

Note: Communication is max 65 feet

Ordering Information

M56	00	-	0	0	00	0	5 -		100P		G
Model	00	•	0	Snubber	00	Label	Pressure Port	-	Pressure Range		Pressure Type
M56	00		0 = 17-4PH	0 = No Selection 1 = Oxygen Clean B40.1 Level IV 2 = With Snubber	00	0 = Adhesive Label 1 = Laser Marking	2 = 1/4-19 BSPP 3 = G3/8 JIS B2351 4 = 7/16-20UNF Male SAE J1926-2 Straight Thread O- Ring BUNA-N 90SH-904 5 = 1/4-18 NPT 6 = 1/8-27NPT B = G1/4 JIS B2351 E = 1/4-19 BSPT F = 1/4-19 BSPP Female P = 7/16-20UNF Female SAE J513 Straight Thread with Integral Valve Depressor Q = M10 x 1.0 mm ISO 6149-2 N = 7/16-20UNF FEMALE SAE J513 Straight Thread S = M12 x 1.5 mm ISO 6149-2 U = G1/4 DIN 3852 Form E Gasket DIN3869-14 NBR W = M20 x 1.5 mm ISO 6149-2 G = M14 x 1.5 mm ISO 6149-2	1	050P 100P 200P 300P 500P 01KP 03KP 05KP 07KP 10KP 15KP	3.5B 007B 010B 020B 035B 070B 200B 350B 500B 700B 01KB	G = Gage S = Sealed C = Compound

Note: Compound pressure range is -14.7 to xxxpsig or -1 to xxxbarg. (e.g. 200PC: -14.7 to 200psig, 020BC: -1 to 20barg)

NORTH AMERICA

Measurement Specialties, Inc., a TE Connectivity company 45738 Northport Loop West Fremont, CA 94538 Tel: +1 800 767 1888

Fax: +1 510 498 1578

<u>customercare.frmt@te.com</u>

EUROPE

MEAS France SAS, a TE Connectivity company 26 Rue des Dames 78340 Les Clayes-sous-Bois, France Tel: +33 (0) 130 79 33 00

Fax: +33 (0) 134 81 03 59 customercare.lcsb@te.com

ASIA

Measurement Specialties (China) Ltd., a TE Connectivity company No. 26 Langshan Road Shenzhen High-Tech Park (North) Nanshan District, Shenzhen, 518057 China

Tel: +86 755 3330 5088 Fax: +86 755 3330 5099 customercare.shzn@te.com

te.com/sensorsolutions

Android is a trademark of Google Inc.

Google Play is a trademark of Google Inc.

iOS is a trademark or registered trademark of Cisco in the U.S. and other countries and is used under license.

Microsoft, Encarta, MSN, and Windows are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries.

Android and Windows are trademarks of their respective owners.

The Bluetooth[®] word mark and logos are registered trademarks owned by the Bluetooth SIG, Inc. and any use of such marks by TE Connectivity is under license. Other trademarks and trade names are those of their respective owners.

Measurement Specialties Inc., a TE Connectivity company.

Microfused, Measurement Specialties (MEAS), American Sensor Technologies (AST), TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2016 TE Connectivity Ltd. family of companies All Rights Reserved.

