

Insulation Support ?	Insulation Support
Wire/Cable Type ?	Stranded
Insertion Force ?	Normal
Finish ?	Tin

Mechanical Attachment

Board Mount ?	No
--------------------------------------	----

Termination Features

Crimp Type ?	F-Crimp
-------------------------------------	---------

Dimensions

Mating Area Interface Dimensions (mm [in]) ?	6.35 x 0.81 [.250 x .032]
---	---------------------------

Insulation Diameter (mm [in]) ?	3.00-4.29 [.118-.169]
--	-----------------------

Body Features

Weld Tab ?	Without
-----------------------------------	---------

Wire Range (mm [AWG]) ?	1.00-2.50 ² [17-13]
--	--------------------------------

Material ?	Brass
-----------------------------------	-------

RoHS/ELV Compliance ?	RoHS compli
--	-------------

Lead Free Solder Processes ?	Not re proces
---	------------------

RoHS/ELV Compliance History	Always compli
------------------------------------	------------------

UL Rating	Listed
------------------	--------

CSA Certified	Yes
----------------------	-----

Conditions for Usage

For Hermetic Header Tab ?	Yes
--	-----

Packaging Features

Packaging Method ?	Loose
---	-------

Packaging Quantity	500/B
---------------------------	-------

Other

Line ?	Premie
-------------------------------	--------

Brand	AMP
--------------	-----

Corporate Information

[About TE](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

[Terms & Conditions](#)

[Privacy Policy](#)

[Global Accessibility Statement](#)

Quick Links

[Distributor Inventory](#)

[Product Cross Reference](#)

[Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Knowledge Base](#)

[Manage Your Account](#)