

Testo 316-3 Refrigerant Leak Detector

Rugged and Reliable

Testo 316-3 is a reliable refrigerant leak detector that delivers dependable, rugged performance at a great value. The proven heated diode sensor provides great sensitivity down to 0.15 ounces/year including the new refrigerant blends like R-410A, R-407C, and R-134a.

Just turn it on and start getting readings immediately! Thanks to the automatic zeroing, the testo 316-3 is extremely fast and can be used even in previously contaminated areas.



Features

- Designed for use on new refrigerants and blends
- Patented heated diode sensor provides excellent sensitivity
- High/low sensitivity adjustment
- Easy one button operation
- Automatic zeroing
- LED indicator and audible alarm
- Rugged housing

Testo 316-3 Refrigerant Leak Detector

testo 316-3, refrigerant leak detector

Includes: sensor head, transport case, calibration certificate, batteries and filter

Part no. 0563 3163



Technical data sensor

Sensitivity	0.15 oz/yr; (4g/a)
-------------	--------------------

General technical data

Detectable refrigerants	R-22, R134a, R-404A, R-410A, R-507, R438A and all CFCs, HFCs, and HCFCs
Conformance	SAE J1627, EN 14624, EG 2004/108/EG
Operation temp.	-4 to 122 °F
Operation humidity	20 to 80 %RH
Storage temp.	32 to 122 °F
Battery type	2 x D
Battery life	16 hours continuous
Weight	1 lb.
Warranty	2 years

Accessories

	Part no.
316-3 Replacement sensor	0554 2610