

FEATURES

- Ergonomic Design
- Beep Feedback
- IP42 Rated
- Hands Free Mode

RS PRO BARCODE SCANNERS

RS Stock No.: 2343218



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- *This item is an image-based handheld barcode scanner that combines appearance and performance. Equipped with the 1st Generation self-developed recognition, analysis algorithms and optics. Not only can it read all ordinary 1D liner barcodes and 2D barcodes, but also read damaged, wrinkled, stained, low-contrast barcodes and more.*
- *Super easy to use, no need to install any drivers, it can be used for most operating systems. With its superior performance and ergonomic design, it is still favoured by many customers in retail and service fields.*
- *This barcode scanner is equipped with an outstanding CPU. This CPU-based scanner can effortlessly capture high-density, high-volume, and distorted barcodes printed on paper or displayed on screen.*
- *This scanner is IP42 rated and drop resistant up to 1.2m, with no moving parts, this item is sturdy inside and out.*
- *This barcode scanner is a new age device that rapidly reads 1D codes : **EAN/UPC, Code128, Code39, Code93, CodaBAR, Code32, Code11, Interleaved 2 of 5, Industrial 2 of 5, Matrix 2 of 5, MSI, GS1.***
- *This barcode scanner is a new age device that rapidly reads 2DQR code : **QRcode, Data matrix, PDF417.***

General Specifications


| | |
|----------------------------|--|
| Model: | C1271 |
| Sensitivity: | Rotate: 360° Deflection: $\pm 35^\circ$ Tilt: $\pm 45^\circ$ |
| Specifications | 2343218-STD |
| Algorithms: | HEROJE 1st -Generation |
| Resolution: | 640*480 |
| Minimum precision: | 4mil |
| Depth of Field: | 32mm-232mm (UPC 13mil) |
| Min. Contrast: | 30% |
| Decoding Frequency: | 300 scans/sec |
| Scan Angle: | Roll: 360°, Pitch: $\pm 60^\circ$, Skew: $\pm 65^\circ$ |
| Storage Function: | NO |
| Scan Feedback: | Beep, LED Light |
| Dimensions: | 170mm (L) 60mm (W) 95mm (H) |
| Weight: | 165g |
| Interfaces: | USB |
| Decode: | <ul style="list-style-type: none"> ● 1D: EAN/UPC, Code128, Code39, Code93, CodaBAR, Code32, Code11, Interleaved 2 of 5, Industrial 2 of 5, Matrix 2 of 5, MSI, GS1. ● 2D: QRcode, Data matrix, PDF417. |

Approvals

| | |
|----------------------------------|------|
| Compliance/Certifications | CE |
| Declarations | ROHS |

Dimension and Wiring

***Depth Of Field, Reading Range**



| Typical 1D mil size | Depth of Field (mm) | |
|------------------------|---------------------|---------|
| | Inside | Outside |
| 5 | 10 | 80 |
| 7.5 | 25 | 155 |
| 10 | 35 | 175 |
| 15 | 50 | 250 |
| 20 | 80 | 325 |
| 30 | 85 | 440 |
| 50 | 75 | 480 |

***Note:** Minimum 1D element is typically 1/2 the size of minimum 2D element.
 Example: 10mil 2D = 5mil 1D