


# AVERY DENNISON MARKETING SPECIFICATION

## HISTORY

THE SUBJECT MATTER DISCLOSED HEREIN EMBODIES PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF THE AVERY DENNISON CO. NONE OF WHICH SHALL BE COPIED, REPRODUCED, DISCLOSED TO OTHERS, PUBLISHED OR USED IN WHOLE OR IN PART, FOR ANY PURPOSE OTHER THAN THAT FOR WHICH IT IS BEING MADE AVAILABLE WITHOUT THE EXPRESS ADVANCE WRITTEN PERMISSION OF A DULY AUTHORIZED AGENT OF THE COMPANY. THIS DOCUMENT IS THE PROPERTY OF THE AVERY DENNISON CO. AND IS TO BE RETURNED TO THE COMPANY ON DEMAND.

REV.	DATE	DESCRIPTION
M	10.29.14	REDRAWN IN NEW FORMAT, ADDED UL INFORMATION AND LOGO



NOTE: THESE CABLE TIES ARE PLENUM RATED AND HAVE A FLAMMABILITY RATING OF V-2



LOOP TENSILE STRENGTH:	40 LBF/180 N MIN. PER AS-23190	APPROVALS:	ENG. APPR.	<i>MLO dr</i> 7/26/2017	<b>AVERY DENNISON</b> <small>FASTENER DIVISION                      FRITCHBURG, MA 01420 U.S.A.                      TEL. 1-800-225-5913                      FAX. 978-353-8157</small>
OPERATING TEMP RANGE:	-40°F (-40°C) TO 221°F (105°C)		Q.A. APPR.	<i>J. Boyce</i> 7/26/2017	
MIN. INSTALLATION TEMP:	32°F (0°C)				
WEIGHT:	0.72 g. / (0.02448 oz.)	SPECIFIED TOLERANCES ARE:	MATERIAL	DESCRIPTION	
BUNDLE DIAMETER:	∅ 1.6mm TO ∅ 76.2mm (0.06" - 3.0")	.XX ± .03 INCHES .X ± .7 MM	<b>NYLON 6/6, HEAT STABILIZED</b>	<b>11" CABLE TIE, LADDER</b>	
TOOL:	12001-0 - HAND TOOL 12500-0 - PNEUMATIC TOOL	.XXX ± .010 INCHES .XX ± .25 MM	COLOR	STOCK NO.	REV.
PACKAGING:	1000/BAG, 5000/CASE	ANGULAR: ± 2°	<b>BLACK</b>	<b>08473-0</b>	<b>M</b>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Avery Dennison:](#)

[08473-0 5000/PACK](#) [08473-0](#)