PRODUCT SPECIFICATION

Brand C.K

Product Range PVC pipe cutters
Catalogue number 2238, 2239 & 2240

Date 14/05/2014



Range Description

Ratchet PVC Pipe cutters

Features

430001

- Glass fibre reinforced body strong and lightweight
- Ergonomic handle design for increased leverage
- Razor sharp stainless steel blade for corrosion protection and performance



430001

Features

430003

- Heavy duty cast Aluminium body for strength
- Ratchet cutting mechanism for effortless clean cuts
- Razor sharp stainless steel blade for corrosion protection and performance
- Cable trunking adaptor included for convenience
- Cuts a wide variety of plastic and rubber products



With trunking adaptor

430003

Features

T2240

- Aluminium Anvils and handles lightweight and comfortable
- Razor sharp stainless steel blade for corrosion protection and performance
- Supplied with 5 different anvils: general purpose anvil, 90 degree square anvil, multi angle anvil, 25mm single radius anvil and double radius anvil
- Quick and easy anvil hanging for convenience and speed



T2240

| Item Number | Item Description | EAN No | Commodity code | Carton Qty |
|----------------|-------------------------|---------------|----------------|---------------|
| 430001 | PVC conduit pipe cutter | 5051074300010 | 82034000 | 3 |
| 430003 | Ratchet conduit cutter | 5051074300034 | 82034000 | 3 |
| T2240 | Multi cutter | 5013969062847 | 82034000 | 3 |

Technical product information

430001

Body – Glass fibre reinforced plastic Blade – Stainless steel

Capacities:

Cuts up to 28mm diameter (11/4")

Suitable for cutting PVC conduit, Blue water mains plastic pipe, rubber/plastic hose, Pneumatic pipes, electrical sleeving etc.

430003

Body – Die cast Aluminium Blade – Stainless steel

Capacities:

Cuts up to 32mm diameter (11/4") PVC pipe/conduit Can also be used to cut plastic water pipe, hose pipe, electrical sleeving, cable trunking, etc.

T2240

Body – Die cast Aluminium Blade – Stainless steel

Capacities

| | For PVC Pipe & Hose Jaw anvil of 17mm & 20mm | | Max capacity 3mm | | | | | |
|------------------------------------|---|--|---|--|--|--|--|--|
| | 90° Square anvil | | Max capacity 2mm | | | | | |
| | Flat anvil General flat material cutting | | For laminated soft wood less than 10mm Also will cut 2mm thick square section trunking up to 35mm wide | | | | | |
| | Multi-angle anvil Cutting for 45°, 75°, 90°, 105°, 120° angles | | For laminated soft wood less than 10mm | | | | | |
| | For PVC Pipe & Hose Jaw anvil of 27mm dia. | | Max capacity 3mm | | | | | |
| | Can be used to cut plastic trim, conduit, trunking, hose, PVC pipe, wooden dowel etc. | | | | | | | |
| | Note These products are not designed to cut wire, metal or reinforced tubi attempting to cut such materials will damage the blade | | | | | | | |
| Standards compliance | None applicable | | | | | | | |
| User health and safety information | None applicable | | | | | | | |
| RoHS/WEEE | This product range does not fall within the scope of RoHS or WEEE | | | | | | | |
| compliance Material safety data | regulations None applicable | | | | | | | |
| Warranty | C.K cutters are guaranteed for life against imperfect materials or | | | | | | | |
| ŕ | workmanship The cutter working mechanism and the cutting edge of the blade will wear over time, this is not covered under the terms of the warranty | | | | | | | |
| Country of origin | Taiwan | | | | | | | |

Dimensional details

| | Product only | | | | Product on primary packaging | | | |
|--------|--------------|----------|-----------|--------------|------------------------------|----------|-----------|-------------------|
| Item | Width mm | Depth mm | Height mm | Net weight g | Width mm | Depth mm | Height mm | Gross weight g |
| 430001 | 72 | 25 | 195 | 166 | 130 | 28 | 280 | 200 |
| 430003 | 94 | 30 | 205 | 360 | 130 | 35 | 280 | 410 |
| T2240 | 80 | 25 | 210 | 461 | 230 | 40 | 295 | 559 |

| | Shelf box (| secondary p | Euro Pallet data Wi x Hi | | | |
|--------|-------------|-------------|-----------------------------|-------------------|-----------------------|---------------------|
| Item | Width mm | Depth mm | Height mm | Gross weight g | No of cartons on base | Number of rows high |
| 430001 | 227 | 295 | 57 | 717 | | |
| 430003 | 290 | 370 | 37 | 1365 | | |
| T2240 | 235 | 305 | 80 | 1882 | | |

Packaging waste details

| | Primary Packaging | | | | Secondary packaging | | | |
|--------|-------------------|---------|--------|-----------------|---------------------|-----|--------|-----|
| Item | Plastic g | Use | Card g | Use | Plastic g | Use | Card g | Use |
| 430001 | 16 | Blister | 18 | Backing card | | | 117 | Box |
| 430003 | 22 | Blister | 28 | Backing card | | | 135 | Box |
| T2240 | 85 | Blister | 13 | Backing card | | | 205 | Box |