

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0348033211](#)
Status: **Active**
Overview: [Stac64 Single, Multi-Pocket and Hybrid Header System](#)
Description: [CTX64 Female Terminal, Tin, S-Grip, D-Wind, Left Payoff, SAE 22](#)

Documents:

Drawing (PDF)	Packaging Specification PK-31301-053 (PDF)
Product Specification PS-502306-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-502306-002-001 (PDF)	Product Literature (PDF)

General

Product Family	Crimp Terminals
Series	34803
Application	Signal
Crimp Quality Equipment	Yes
Overview	Stac64 Single, Multi-Pocket and Hybrid Header System
Product Literature Order No	987650-4561
Product Name	CTX64
UPC	887191519272

Physical

Gender	Female
Grip Code	S
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.114/g
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.10 to 1.65mm
Wire Size AWG	22
Wire Size mm ²	0.22-0.35

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	14V DC

Material Info

Reference - Drawing Numbers

Application Specification	AS-502306-002-001
Packaging Specification	PK-31301-053
Product Specification	PS-502306-001-001
Sales Drawing	SD-31301-053, SD-34803-002-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2018 (15
January 2018)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[34803](#) Series

Use With

[34729](#) 2.54mm Pitch Stac64 Right Angle Receptacle

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION