

## Data sheet

Commercial Art.No.: 70.320.1028.0

Bottom BAS GUT GA 10 A

revos BASIC size 10 open-bottom bases, double locking lever

1011011010001010010101101  
 0100110110010110100101010  
 101001101100111001010010  
**DIGITALIZATION  
 IN PROGRESS**  
 10101001101010101001010  
 1101010011011001011010010  
 10101010010101101010011

Commercial Art.No.	70.320.1028.0
EAN	4015573220058
Order Unit	1

Certificates / Approvals



## Technical data

### General

Housing material	Aluminium
Color	Grey
Surface	With powder coating
Degree of protection (IP)	IP54
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

### Model

Construction	10
Model	Equipment mounted (feed-through)
Locking mechanism	Double locking levers
Cable entry	None
Type of cable	None
With cable screw gland	No
Thread size PG	
Hinged lid	No
EMC-version	No
Length	93 mm
Width	43 mm
Height	28 mm

### Classification

ECLASS 8.1	27440202
ETIM 7.0	EC000437
ETIM 6.0	EC000437
ETIM 5.0	EC000437

ETIM 4.0	EC000437
----------	----------