



NOTES:  
 MATERIAL: CONTACTS:PHOSPHOR BRONZE  
 INSULATOR:PBT+30% GLASS UL 94V-0  
 ELECTRICAL:  
 CONTACT CURRENT PATING:1A  
 DIELECTRIC WITHSTANDING VOLTAGE: 1000V AC  
 CONTACT RESISTANCE: 20milliohms max  
 INSULATION RESISTANCE: 1000 MEGOHMS  
 CAPACITANCE:0.5PICO-FARAD MAXIMUM  
 TEMPERATURE RANGE:-40°C+105°C  
 MECHANICAL:  
 ENGAGING FORCE:340g/A CONTACT MAX.  
 SEPARATING FORCE:20g/A CONTACT MIN.  
 DURABILITY:50 CYCLES  
 NO.OF CONTACT:6-48  
 FINISH:  
 CONTACT PLATING:TIN PLATED 6C.03U"-88.35U"



PCB LAYOUT

PIN NO.	DIM A	DIM B	DIM C	DIM D
8	10.16	7.62	7.62	10.16
14	17.78	15.24	7.62	10.16
16	20.32	17.76	7.62	10.16
18	22.86	20.32	7.62	10.16
20	25.4	22.86	7.62	10.16
22	27.95	25.4	7.62	10.16

DATE	DR.BY	ECN.NO.	DESCRIPTION	MARK	VER.
2011/06/21	XIE		NEW DWG		A0
-TOLERANCES- UNLESS OTHERWISE SPECIFIED					
X.X	±0.30	X.X	±3.00	APPD:	
X.XX	±0.25	X.XX	±1.00	CHECK:	
X.XXX	±0.100	X.XXX	±0.500	DRAW:	
			<b>CnC Tech,LLC</b> <b>Industrial Cable and Connector Technology</b>		
			TITLE: Low Cost Version IC Socket, Retentive Leg, 7.62MM Pitch		
			PRODUCT NO: 245-XX-1-03		
X.X	±0.30	X.X	±3.00	APPD:	
X.XX	±0.25	X.XX	±1.00	CHECK:	
X.XXX	±0.100	X.XXX	±0.500	DRAW:	
			DATE	SCALE	UNIT
			2011/06/21	1:1	mm
					Z
					1/1