


Specifications:
 Current Rating: 1.5A AC/DC
 Voltage Rating: 30V AC/DC
 Contact Resistance: 30m ohm. Max.
 Insulation Resistance: 1,000M ohm. min.
 Withstanding Voltage: 500V AC For One Minute
 Operating Temperature Range: -40°C ~ +105°C

Material and Finish
 Insulator: PBT (UL94V-0)
 Color: White
 Contact: Brass
 Plating: 30u" Gold Plated on Contact Area,
 Tin Plated on Solder Tail.
 Shell: Brass, Nickel Plated



RoHS Compliant

REV	DATE	FILE	BY
	05-FEB-2020		

DRAWN:
CHECKED:
APPROVAL:

GENERAL TOLERANCE: .X=±0.20 .XX=±0.10
UNIT: MM
SCALE: 1:1
SHEET: 1 / 2
PROJECTION:

DESCRIPTION: Industrial Cable and Connector Technology
PART NO.: USB A PCB Socket Straight, 30u"
SIZE: A4

1002-001-01000
