




RoHS

REV.	DESCRIPTION	DATE
A	RELEASE	2012.11.12

NOTES:

- Insulator Material: Nylon-6T, UL 94V-0
- Contact Plating: Flash Gold
- Contact Material: Brass
- Current Rating : 1A AC,DC
- Contact Resistance: 20MΩ Max.
- Dielectric Withstanding: AC 500V
- Insulator Resistance: 1000MΩ Min.
- Operating Temp.: -40°C~+105°C



Recommended PCB Layout

NUMBER OF POSITIONS	DIMENSIONS		
	A	B	C
10	5.08	11.25	12.65
14	7.62	13.79	15.19
16	8.89	15.06	16.46
20	11.43	17.60	19.00
26	15.24	21.41	22.81
30	17.78	23.95	25.35
34	20.32	26.49	27.89
40	24.13	30.30	31.70
50	30.48	36.65	38.05
60	36.83	43.00	44.40

UNLESS TOLERANCE	
GENERAL	ANGLE
X ± 0.30	X° ± 3.0°
.X ± 0.25	.X° ± 2.0°
.XX ± 0.20	.XX° ± 1.0°
.XXX ± 0.10	.XXX ± 0.5°

DESIGN BY	DRAW BY	SCALE	SHEET	UNIT	MM	DRAW NO:	REV: A
CHECK BY	APPROVE BY	1:1	1/1			3220-XX-0100-00	
Cnc Tech,LLC							
Port NO. 3220-XX-0100-00							