


PIN ASSIGNMENT:

Electrical test:

1. 100% short, open, miswire test
2. Conduct resistance: $2\ \Omega_{\text{m(max)}}$
3. Insulation resistance: $10\text{M}\Omega_{\text{m(min)}}$
4. dielectric test: DC 300V



⑦	PE BAG	1/5	CLEAR SIZE: 330*380*0.05mm PRINT BLACK"MADE IN CHINA"+"5PCS"及印生产周期, 有透气孔.
⑧	PE BAG	1	CLEAR SIZE: 210*250*0.05mm PRINT BLACK"MADE IN CHINA"+"1PC"及印生产周期, 有透气孔.
⑤	TIE	1	BLACK L=80mm
④	OUT JACKET	12g	BLACK PVC-50P (MOULD NO:WM-40 & WM-88)
③	CABLE	1	BLACK USB2.0 UL2725 28#/1P+28#/2C+4EB OD:3.8mm L=5000±15
②	CONN	1set	USB2.0 刺破式 A/TYPE MALE SHELL:NICKEL PIN:G/F 4PCS TYPE INSULATOR COLOR:WHITE
①	CONN	1set	USB2.0 刺破式 MINI 5P MALE SHELL:NICKEL PIN:G/F 3PCS INSULATOR COLOR:BLACK
NO.	NAME	Q'TY	SPECIFICATION

CnC Tech, LLC			
Industrial Cable and Connector Technology			
DRAWED	ZHONGHS	DRAWING NO	
CHECKED		CUSTOMER	
APPROVAL		ITEM NO.	102-1031-BL-00500
DECIDED		DATE	2012-02-16
VERSIONS/EDITOR	A/0	PROJECTION	