



UNIT: mm




CABLE BLACK PRINT
 HI-SPEED USB Revision 2.0 SHIELDED 28AWG/1P+24AWG/2C
 E189529 **RA** AWM STYLE 2725 80° C 30V VW-1 VEGA TECH

PIN ASSIGNMENT:



Electrical test:
 1. 100% short, open, miswire test
 2. Conduct resistance: 2 Ohm(max)
 3. Insulation resistance: 5Mohm(min)
 4. dielectric test: DC 300V

IPCS/PE BAG



③	PE BAG	1/10	CLEAR SIZE: 280*330*40. 05mm PRINT BLACK "MADE IN CHINA" + "10PCS"
⑦	PE BAG	1	CLEAR SIZE: 130*230*40. 05mm PRINT BLACK "MADE IN CHINA" + "1PC"
⑥	TIE	1	WHITE L=100mm
③	OUT JACKET	6g	BEIGE (1V-29#) PVC-40P (MOULD NO: WM-65)
④	OUT JACKET	6g	BEIGE (1V-29#) PVC-40P (MOULD NO: WM-40)
③	CABLE	1	BEIGE (1V-29#) USB2. 0 UL2725 28#/1P+24#/2C+AEB OD: 4. 7mm l=2000 ± 10mm
⑦	CONN	Iset	USB2. 0 B MALE SHELL: NICKEL. PIN G/F 3PCS TYPE INSULATOR COLOR: WHITE
①	CONN	Iset	USB2. 0 A MALE SHELL: NICKEL. PIN G/F 3PCS TYPE INSULATOR COLOR: WHITE

Cnc Tech, LLC Industrial Cable and Connector Technology			
DRAWN	ZHONGHS	DRAWING NO	
CHECKED		CUSTOMER	
APPROVAL		ITEM NO.	102-1030-BE-00200
DECIDED		DATE	2012-02-14
VERSIONS/EDITION	A/0	PROJECTION	