




**SPECIFICATION
CONTROL DRAWING**
Crystal Resonator

FREQUENCY
24.000000MHz



Holder Style	25x2x05 4-pad
Mode	Fundamental
Adjustment Tolerance	± 10PPM at 25°C
Temperature Stability	± 15 PPM
Operating Temp. Range	-30°C to +85°C
Load Capacitance	16 pF
ESR	100 Ohm
Ageing	+/-1ppm
Marking	AEL24

Amdt Date	Change Note	AEL Code
18 MAR 08	Temp Stability, Op Temp Range and ESR amended	X24M000000S029
		Issue Ref B