

Atlantic, Atlantic-E and Marina cabinets: plain plates and perforated plates



Cabinet and equipment selection chart p. 262-263
 Technical characteristics p. 277

Pack	Cat.Nos	Plain plates				
		Galvanized steel Not compatible with Atlantic-E cabinets				
		Vertical mounting for cabinets			Horizontal mounting for cabinets	
		Height (mm)	Width (mm)	Weight (kg)	Height (mm)	Width (mm)
1	0 360 49 ¹	300	220	0.9		
1	0 360 69	300	300	1		
1	0 360 52	300	400	1.3	400	300
1	0 360 70	400	400	1.7		
1	0 360 56	400	600	3.3	600	400
1	0 360 55	500	400	2.7		
1	0 360 71	500	500	3.5		
1	0 360 57	600	600	6.2		
1	0 360 59	600	800	8.4	800	600
1	0 360 54	600	1000	10.6	1000	600
1	0 360 58	700	500	6		
1	0 360 60	800	800	11.4		
1	0 360 61	800	1000	14.4	1000	800
1	0 360 63	1000	1000	20.5		
1	0 360 65	1000	1200	23	1200	1000
1	0 360 64	1200	800	18.5		
1	0 360 66	1200	1200	34.4		
1	0 360 67 ²	1400	800	26.4		
1	0 360 68	1400	1000	32.2		

Pack	Cat.Nos	Lina 12.5 plates				
		Galvanized steel. With drilling for fixing equipment without marking. Automatic bracket: - Ø6.5 mm for plastic rivet Cat.No 0 366 44 (trunking) - Ø3.3 mm for mounting with screw Cat.No 0 347 45				
		Vertical mounting for cabinets			Horizontal mounting for cabinets	
		Height (mm)	Width (mm)	Weight (kg)	Height (mm)	Width (mm)
1	0 360 00 ²	300	200	0.4		
1	0 360 01 ¹	300	220	0.47		
1	0 360 02	300	300	0.6		
1	0 360 04	300	400	0.8	400	300
1	0 360 05	400	400	1.1		
1	0 360 22	400	600	2.2	600	400
1	0 360 09	500	400	1.5		
1	0 360 14	500	500	1.85		
1	0 360 24	600	600	3.7		
1	0 360 33	600	800	5.2	800	600
1	0 360 40	600	1000	6.8	1000	600
1	0 360 31	700	500	3.7		
1	0 360 34	800	800	7		
1	0 360 42	800	1000	9.2	1000	800
1	0 360 43	1000	1000	11.5		
1	0 360 47	1000	1200	13.9	1200	1000
1	0 360 46	1200	800	11.1		
1	0 360 48	1200	1200	16.7		
1	0 360 75 ²	1400	800	13		
1	0 360 79	1400	1000	16.2		

Pack	Cat.Nos	Lina 25 perforated plates	
		Galvanized steel	
		Common for all types of cabinets	
		For cabinets	Weight (kg)
		Height x Width (mm)	
1	0 360 07 ²	300 x 200	0.4
1	0 360 99 ¹	300 x 220	0.4
1	0 360 91	300 x 300	0.5
1	0 360 11	300 x 400	0.6
1	0 360 12	400 x 300	0.6
1	0 360 92	400 x 400	0.8
1	0 360 13	400 x 600	1.1
1	0 360 15	500 x 400	0.9
1	0 360 93	500 x 500	1.1
1	0 360 16	600 x 400	1.3
1	0 360 17	600 x 600	2.1
1	0 360 06	600 x 800	3.1
1	0 360 08	600 x 1000	3.7
1	0 360 18	700 x 500	2
1	0 360 19	800 x 600	3.1
1	0 360 20	800 x 800	4
1	0 360 94	800 x 1000	5
1	0 360 23	1000 x 600	3.7
1	0 360 21	1000 x 800	4.9
1	0 360 25	1000 x 1000	6.8
1	0 360 10	1000 x 1200	8.5
1	0 360 87	1200 x 800	7.1
1	0 360 88	1200 x 1000	8.5
1	0 360 89	1200 x 1200	10.1
1	0 360 90 ²	1400 x 800	7.8
1	0 360 98	1400 x 1000	10



Pack	Cat.Nos	Clip-nuts for perforated plates
		Supplied without screw
100	0 364 40	For M4 screws
100	0 364 41	For M5 screws
100	0 364 42	For M6 screws

Pack	Cat.Nos	Accessories
500	0 366 44	Rivet reinforced plastic Ø6 mm for drilling Ø6.5 mm
100	0 347 45	Screw head 4.8 x 16 mm self-drilling, self-tapping for Ø3.3 mm
200	0 347 50	Screw cover for isolation of screw head Cat.No 0 347 45 inside the trunking

1: For Marina cabinets
 2: For Atlantic and Atlantic-E cabinets

Atlantic, Atlantic-E and Marina cabinets: plain plates and perforated plates


■ Mounting principle






Fixing example on Lina 12.5 plate:
 - of a transformer with screws Cat.No 0 347 45
 - of a rail
 - of Lina 25 cable ducting (p. 328)

■ Dimensions

Assembled chassis with rails and Lina 25 uprights



Lina 12.5 plain plates and Lina 25 perforated plates



Dimensions of cabinets Height x Width (mm)	Uprights height A (mm)	Rail length D (mm)	Chassis fixing	
			B (mm)	C (mm)
300 x 300	237	243	225	225
300 x 400	237	343	225	325
400 x 300	337	243	325	225
400 x 400	337	343	325	325
400 x 600	337	543	325	525
500 x 400	437	343	425	325
500 x 500	437	443	425	425
600 x 400	537	343	525	325
600 x 600	537	543	525	525
600 x 800	537	743	525	725
600 x 1000	537	943	525	925
700 x 500	637	443	625	425
800 x 600	737	543	725	525
800 x 800	737	743	725	725
800 x 1000	737	943	725	925
1000 x 600	937	543	925	525
1000 x 800	937	743	925	725
1000 x 1000	937	943	925	925
1000 x 1200	937	1143	925	1125
1200 x 800	1137	743	1125	725
1200 x 1000	1137	943	1125	925
1200 x 1200	1137	1143	1125	1125
1400 x 800	1337	743	1325	725
1400 x 1000	1337	943	1325	925

Cabinets dimensions Height x Width (mm)	Dimensions of plates Plain / Lina 12.5 / 25 plates		Usable space for equipment (dm ²)	Mounting of plates	
	G (mm)	H (mm)		F (mm)	E (mm)
300 x 200	256	156	4.2	225	125
300 x 220	275	192	5.3	263	163
300 x 300	256	256	6.2	225	225
300 x 400 ⁽¹⁾	256	356	8.2	225	325
400 x 300 ⁽¹⁾	356	256	8.2	325	225
400 x 400	356	356	11.7	325	325
400 x 600 ⁽¹⁾	356	556	18.7	325	525
500 x 400	456	356	15.2	425	325
500 x 500	456	456	19.2	425	425
600 x 400 ⁽¹⁾	556	356	18.7	525	325
600 x 600	556	556	29.7	525	525
600 x 800 ⁽¹⁾	556	756	40.7	525	725
600 x 1000 ⁽¹⁾	556	956	51.7	525	925
700 x 500	656	456	28.7	625	425
800 x 600 ⁽¹⁾	756	556	40.7	725	525
800 x 800	756	756	55.7	725	725
800 x 1000 ⁽¹⁾	756	956	71.7	725	925
1000 x 600 ⁽¹⁾	956	556	51.7	925	525
1000 x 800 ⁽¹⁾	956	756	70.7	925	725
1000 x 1000	956	956	89.7	925	925
1000 x 1200 ⁽¹⁾	956	1156	108.7	925	1125
1200 x 800	1156	756	85.7	1125	725
1200 x 1000 ⁽¹⁾	1156	956	108.7	1125	925
1200 x 1200	1156	1156	131.7	1125	1125
1400 x 800	1356	756	100.7	1325	725
1400 x 1000	1356	956	127.7	1325	925

1: For horizontal or vertical mounting