


ECO



LED FLEXI STRIP

Product Features

- Ultra low power consumption
- Easy installation and flexibility
- Excellent heat management
- Epistar LEDs
- 30,000 hours working life
- Precise LED binning section enables 100% consistent colour temperature from batch to batch
- Multiple applications for commercial and residential environments
- 3M adhesive back



Cool White



Warm White

ECO



Low Power Economical LED Flexistrip Series


Model	• F8-C3528-12-30-IP20	• F8-W3528-12-30-IP20
Colour	<input type="checkbox"/> Cool White	<input type="checkbox"/> Warm White
CCT (K)	5700-6300K	2700-3300K
CCT (K) Nominal	6000K	3000K
LED's per metre	30	30
Power per metre	2.4W	2.4W
Available IP Ratings	IP20	IP20
Input Voltage	12V	12V
Cutttable length	100mm	100mm
Length	5m	5m
Lumens	190lm	160lm
Angle (°)	120°	120°

The Eco range of LED flexistrips offer an ultra lower power unit with IP20 ratings, for reduced running costs.

IP20 Rated - Protected from finger sized foreign objects.
No protection from water.

Dimensions L x W x H (mm): 5000 x 8 x 2.2

ECO Series Mechanical



Maximum length = 5m