

# **SPECIFICATION**

Part No. : CAB.S01

Product Name : Taoglas Cable Assembly

IPEX MH4(HSC comp) to SMA(F)Bulkhead Straight Connector


with 100mm  $\emptyset$ 0.81 cable

Photo :






### 1. Cable Insertion Loss



## 2. 0.81 Cable Specification

## 2.1 Drawing - Cross Section





#### 2.2 Structure and Dimensions




### 2.3 Electrical & Physical Specification

1	Insulation Resistance:	1000 MEGA OHM-KM Min.		
2	Conductor Resistance:	1400 OHM/KM/20°C Max.		
3	Dielectric Strength:	AC 1.0 KV/minute		
4	Spark test:	2.5 KV		
5	Nom. Impedance	50 ± 3 Ohms		
6	Nom. Capacitance	97 ± 3 pF/m		
7	Attenuation (dB/1M)	2.0GHz 3.60		
		2.4GHz 5.10		
		3.0GHz 6.20		
		4.0GHz 7.50		
		5.0GHz 8.50		
		6.0GHz 9.40		



# 3. Technical Drawing


### 3.1 CAB.S01




	Name	Part No.	Material	Finish	QTY
1	SMA(F) ST	SMA.F.ST.JACK.B.W	Brass	Gold	1
2	0.81 Cable	OD.081.W	FEP	Gray	1
3	Heat Shrink Tube	001312E000014A	PE	Black	1
4	IPEX MHF4	IPEX.MHF4.081	Brass	Gold	1
5	Washer	See Connector Spec	Brass	Gold	1
6	Nut	See Connector Spec	Brass	Gold	1



#### 3.2 Connectors




# 3.3Recommended Mounting Hole - SMA(F) Bulkhead





## 4. Packaging



(327x280x218mm)



Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice.

Taoglas reserves the rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

Copyright © Taoglas Ltd.