




**SS011**

**Stainless Steel Metric Double Ring  
End Offset Wrenches**



**PRODUCT DETAILS**



- AISI 420 stainless steel body
- Magnetic
- High strength and hardness
- Can be Autoclave Sterilized at 121°C
- Produced according to ISO 1085, ISO 10104 and DIN 838



**Follow the Fish!**



## PRODUCT ATTRIBUTES

Product		a1	a2	b1	b2	L	 g
<b>SS011-0507</b>	5.5*7 mm	7 mm	8 mm	12 mm	13 mm	180 mm	55 g
<b>SS011-0607</b>	6*7 mm	7 mm	8 mm	12 mm	13 mm	180 mm	55 g
<b>SS011-0809</b>	8*9 mm	7 mm	8 mm	14 mm	17 mm	190 mm	55 g
<b>SS011-0810</b>	8*10 mm	7 mm	8 mm	14 mm	17 mm	190 mm	55 g
<b>SS011-0911</b>	9*11 mm	8 mm	9 mm	17 mm	20 mm	215 mm	75 g
<b>SS011-1012</b>	10*12 mm	8 mm	9 mm	17 mm	20 mm	215 mm	75 g
<b>SS011-1214</b>	12*14 mm	9 mm	10 mm	20 mm	23 mm	225 mm	100 g
<b>SS011-1417</b>	14*17 mm	10 mm	11 mm	23 mm	27 mm	255 mm	160 g
<b>SS011-1618</b>	16*18 mm	11 mm	12 mm	27 mm	30 mm	280 mm	200 g
<b>SS011-1719</b>	17*19 mm	11 mm	12 mm	27 mm	30 mm	280 mm	200 g
<b>SS011-1722</b>	17*22 mm	12 mm	13 mm	30 mm	35 mm	300 mm	260 g
<b>SS011-2224</b>	22*24 mm	13 mm	14 mm	35 mm	38 mm	330 mm	360 g
<b>SS011-2427</b>	24*27 mm	14 mm	15 mm	38 mm	42 mm	340 mm	500 g
<b>SS011-2430</b>	24*30 mm	15 mm	16 mm	42 mm	46 mm	350 mm	580 g
<b>SS011-3032</b>	30*32 mm	16 mm	17 mm	46 mm	49 mm	370 mm	600 g

