

## Power It! 6-Outlet Power Strip, 6 ft. (1.83 m) Cord, Power Switch Cover

MODEL NUMBER: TLM606NC



### Highlights

- 6 outlets
- Illuminated on/off switch with cover
- 15-amp circuit breaker
- 6-ft. (1.83 m) power cord
- Rugged metal case
- Keyhole mounting slots

### Package Includes

- TLM606NC power strip
- Warranty information
- Instruction manual

### Description

Tripp Lite's Power It! TLM606NC power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment. Includes 6 NEMA 5-15R outlets, 6-ft. (1.83 m) AC power cord and keyhole mounting slots. Multi-outlet strip reduces cable clutter and enables the connection of multiple electrical devices to a single AC wall socket. Features rugged metal case to stand up to the most demanding environments, illuminated power switch with transparent cover to prevent accidental shutoff and 15A integrated circuit breaker to prevent dangerous overloads. INPUT/OUTPUT: Input: NEMA 5-15P/Output: 6 NEMA 5-15R  
ELECTRICAL: 120V AC, 50/60Hz, 15A  
FORMAT: Corded power distribution strip

### Features

- Multi-outlet power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment
- Includes 6 NEMA 5-15R outlets
- Illuminated on/off switch provides one-touch power control for connected equipment
- Transparent switch cover snaps tight to prevent accidental shutoff
- Convenient keyhole slots provide secure mounting options for a wide variety of surfaces and applications
- 15A power handling capacity with integrated circuit breaker
- 120V AC, 50/60Hz electrical compatibility
- 6-ft. (1.83 m) AC line cord
- Rugged metal case provides extra safety and durability
- UL certification

## Specifications



<b>OVERVIEW</b>	
UPC Code	037332127426
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
Integrated Cord Clip	No
<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Overload Protection	15A circuit breaker
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 6
Right-Angle Outlets	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	Illuminated on/off switch controls power to all outlets
Locking Switch Cover	Transparent switch cover snaps tight to prevent accidental shutoff
<b>PHYSICAL</b>	
Color	Light Gray
Antimicrobial Coating	No
Power Cord Color	Light Gray
Housing Color	Light Gray
Integrated Keyhole Mounting Slots	Yes (Includes flanges)
Keyhole Slot Mounting Measurement (Center to Center)	Distance between keyhole slots = 203.20mm; Distance between end tabs = 330.17mm
Material of Construction	Metal



Outlets Measurement (Center to Center)	41.30mm
Receptacle Color	Light gray
Shipping Dimensions (hwd / cm)	36.83 x 12.70 x 6.35
Shipping Dimensions (hwd / in.)	14.50 x 5.00 x 2.50
Shipping Weight (kg)	0.95
Shipping Weight (lbs.)	2.10
Unit Dimensions (hwd / cm)	34.92 x 6.99 x 5.08
Unit Dimensions (hwd / in.)	13.75 x 2.75 x 2
Unit Weight (kg)	0.91
Unit Weight (lbs.)	2
<b>STANDARDS &amp; COMPLIANCE</b>	
Canada	cUL
UL1363 (Power Tap)	UL1363
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[TLM606NC](#)