



Обозначения	Аналог	Структура	P _к max, Вт	U _{кб} max, В	U _{кэ} max, В	U _{эб} max, В	I _к max, А	h _{21е}	U _{кэ} нас. при			f _{гр.} МГц	Тип корпуса
									В	I _к , А	I _б , А		
КТ209А		PNP	0,2	15	15	10	0,3	20-60	0,4	0,3	0,03	5	ТО-92 (КТ-26)
КТ209Б				15	15	10		40-120					
КТ209В				15	15	10		80 - 240					
КТ209Г				30	30	10		20-60					
КТ209Д				30	30	10		40-120					
КТ209Е				30	30	10		80 - 240					
КГ209Ж				45	45	20		20-60					
КТ209И				45	45	20		40-120					
КТ209К				45	45	20		80 - 240					
КТ209Л				60	60	20		40-120					
КТ209М				60	60	20		80 - 240					