



3805 - MALE STUD, BSP TAPER



maximum working pressure	30 bar 3 MPa 435 psi
working temperature	-25 to 150 °C -13 to 302 °F 248 to 423 °K
vacuum capability	755 mm Hg
body	STAINLESS STEEL 316L
'O'-rings	FKM
collar	STAINLESS STEEL 316L
sealing washer	STAINLESS STEEL 316L

Part Nb	ØD (MM)	C	F (mm)	(mm)	H (mm)	(kg)
	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾
3805 04 10	4	R1/8	10	3	14.5	.008
3805 04 13	4	R1/4	14	3	14.5	.015
3805 06 10	6	R1/8	13	4	18	.012
3805 06 13	6	R1/4	14	4	16.5	.018
3805 08 10	8	R1/8	15	5	19	.014
3805 08 13	8	R1/4	15	6	18	.018
3805 08 17	8	R3/8	17	6	18.5	.025
3805 10 13	10	R1/4	19	6	24	.029
3805 10 17	10	R3/8	19	6	22.5	.03
3805 12 13	12	R1/4	22	7	25	.034
3805 12 17	12	R3/8	22	8	24	.04
3805 12 21	12	R1/2	22	10	23	.046