

## Protect It! 1-Outlet Portable Surge Protector, Direct Plug-In, 750 Joules, Tel/Modem Protection

MODEL NUMBER: TRAVELCUBE



### Highlights

- 1 AC outlet
- Direct plug-in design
- Built-in tel/modem surge protection
- 750 joule rating
- Diagnostic LED displays protection status

### Package Includes

- TRAVELCUBE surge suppressor

### Description

The TRAVELCUBE is designed for convenient portable and economical surge protection. Small and powerful, the TRAVELCUBE features 750 joules and carries \$10K of insurance as well as a lifetime product warranty. Throw it in a briefcase or purse and have quality surge protection wherever you need it — hotel room, dorm, client office — anywhere!

### Features

- Portable wall-mount cube stores easily in any bag or briefcase
- 1 NEMA5-15R AC outlet
- 750 joules of protection shields equipment from harmful surges, spikes and line noise
- Diagnostic LED displays protection status
- Built-in tel/modem surge protection
- UL 1449 rated 3rd Edition
- \$10,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

## Specifications

OVERVIEW	
UPC Code	037332118486
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)



Input Cord Length Details	Direct plug-in
Voltage Compatibility (VAC)	120
Maximum Surge Amps	36000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(1) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(1) Yes
Right-Angle Outlets	Yes
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Diagnostic LED(s)	Yes
Diagnostic LED Details	Built-in LED confirms suppressor "protection present" (red) status
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	750
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	500V
EMI / RFI Filtering	Up to 20 dB
Automatic Shut-Off	No
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
<b>PHYSICAL</b>	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Antimicrobial Coating	No
Form Factors Supported	Direct plug in suppressor supports wall-mounting directly into AC receptacle
Housing Color	Light Gray
Integrated Keyhole Mounting Slots	No
Material of Construction	Plastic
Receptacle Color	Light gray
Shipping Dimensions (hwd / cm)	3.81 x 10.80 x 16.51
Shipping Dimensions (hwd / in.)	1.50 x 4.25 x 6.50
Shipping Weight (kg)	0.09
Shipping Weight (lbs.)	0.20
Unit Dimensions (hwd / cm)	3.78 x 5.49 x 7.80
Unit Dimensions (hwd / in.)	1.49 x 2.16 x 3.07
Unit Weight (kg)	0.08
Unit Weight (lbs.)	.17
<b>SPECIAL FEATURES</b>	
Rotatable Outlets	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Approvals	Exceeds IEEE 587 category A&B specifications
UL1449 3rd Edition (AC Suppression)	UL1449 3RD EDITION
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$10,000&nbsp;<a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a>&nbsp;

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[TRAVELCUBE](#)